



# ArchiTrak<sup>®</sup> AKTM Series

AKTM, AKTMD, & AKTMN TRACK



 **prescolite**  
prescolite.com

 **HUBBELL**  
Lighting, Inc.

# AKTM Series

AKTM, AKTMD, & AKTMN TRACK

AKTMN 2" Dia.



AKTMD 2-3/4" Dia.



AKTM 4" Dia.



Ideal for commercial and retail applications, Prescolite's AKTM Series track heads provide powerful, high quality light in compact 2", 2-3/4", and 4" Diameters.

Available in 2700, 3000, or 3500 Kelvin temperatures and 80+ or 90+ CRI options, AKTM track heads feature a tight, 2-step MacAdam ellipse color consistency while delivering 900 to nearly 3000 lumens.

AKTM track heads are compatible with many forward phase and reverse phase dimming controls and also offer beam spreads from 18° spot to 55° wide flood that are factory configurable to meet almost any application need.\*

Along with providing a sleek outer design, the integral die cast aluminum heat sink provides a minimum of 50,000 hours at 80% lumen maintenance making AKTM track heads a great option for lower energy usage and reduced service costs. The AKTMN and AKTMD are both available with an option accessory holder which fits up to 2 media.

\*See spec sheets for more details and recommended dimming controls.

## ORDERING INFORMATION

EXAMPLE: AKTMNLED9L35K8XFL55BL

<b>AKTMNLED</b>	<b>9L</b>	<b>35K</b>	<b>8</b>	<b>XFL55</b>	<b>BL</b>	
<b>BASE</b>	<b>OUTPUT</b>	<b>COLOR</b>	<b>CRI</b>	<b>BEAM SPREAD</b>	<b>FINISH</b>	<b>ACCESSORIES</b>
AKTMNLED 2" Diameter LED Track Head	9L 900 Delivered Lumens	27K 2700 Kelvin 30K 3000 Kelvin 35K 3500 Kelvin 40K 4000 Kelvin	8 80+ CRI 9 90+ CRI	SP18 18 Degree Cutoff FL35 35 Degree Cutoff XFL55 55 Degree Cutoff	BL Black WH White	<b>Holders<sup>3</sup></b> AKTMNABL Accessory Holder, Black AKTMNAWH Accessory Holder, White <b>Louver/Lenses<sup>2</sup></b> AKTH11BL Honeycomb Louver, Black SL11 Linear Spread Lens DL11 Prismatic Diffusion Lens <b>Color Filter<sup>2</sup></b> AML11 Amber Filter BLL11 Blue Filter GRL11 Green Filter

## ORDERING INFORMATION

EXAMPLE: AKTMDLED15L35K8XFL55BL

<b>AKTMDLED</b>	<b>15L</b>	<b>35K</b>	<b>8</b>	<b>XFL55</b>	<b>BL</b>	
<b>BASE</b>	<b>OUTPUT</b>	<b>COLOR</b>	<b>CRI</b>	<b>BEAM SPREAD</b>	<b>FINISH</b>	<b>ACCESSORIES</b>
AKTMDLED 2 3/4" Diameter LED Track Head	15L 1500 Delivered Lumens	27K 2700 Kelvin 30K 3000 Kelvin 35K 3500 Kelvin 40K 4000 Kelvin	8 80+ CRI 9 90+ CRI	MD25 25 Degree Cutoff FL35 35 Degree Cutoff XFL55 <sup>1</sup> 55 Degree Cutoff	BL Black WH White	<b>Holders<sup>3</sup></b> AKTMDABL Accessory Holder, Black AKTMDAWH Accessory Holder, White <b>Louver/Lenses<sup>2</sup></b> AKTH16BL Honeycomb Louver, Black SL16 Linear Spread Lens DL16 Prismatic Diffusion Lens <b>Color Filter<sup>2</sup></b> AML16 Amber Filter BLL16 Blue Filter GRL16 Green Filter

## ORDERING INFORMATION

EXAMPLE: AKTMLED25L35K8XFL55BL

<b>AKTMLED</b>	<b>25L</b>	<b>35K</b>	<b>8</b>	<b>XFL55</b>	<b>BL</b>
<b>FIXTURE</b>	<b>OUTPUT</b>	<b>COLOR</b>	<b>CRI</b>	<b>BEAM SPREAD</b>	<b>FINISH</b>
AKTMLED 4" Diameter LED Track Head	25L 2500 Delivered Lumens	27K 2700 Kelvin 30K 3000 Kelvin 35K 3500 Kelvin 40K 4000 Kelvin	8 80+ CRI 9 90+ CRI	MD25 25 Degree Cutoff FL35 35 Degree Cutoff XFL55 55 Degree Cutoff	BL Black WH White

NOTES:  
<sup>1</sup>AKTMD XFL55 comes with frosted lens standard  
<sup>2</sup>Accessory Holder required for all accessories  
<sup>3</sup>Accommodates up to 2 accessories

