




Straight Blade Devices

Commercial Grade Duplex Tamper-Resistant Receptacles




15A and 20A 125V Self-Grounding Tamper-Resistant Receptacles





Wiring		Side Wired		Back and Side Wired	
Rating	Color	Standard	Standard*	Decorator	Decorator, Nightlight
NEMA 5-15, 15A 125V 	Black	CRS15BLKTR	CBRS15BLKTR	DRS15BLKTR	—
	Brown	CRS15TR	CBRS15TR	DRS15TR	—
	Gray	CRS15GRYTR	CBRS15GRYTR	DRS15GRYTR	—
	Ivory	CRS15ITR	CBRS15ITR	DRS15ITR	DRS15NLI
	Light Almond White	CRS15LATR CRS15WTR	CBRS15LATR CBRS15WTR	DRS15LATR DRS15WTR	DRS15NLLA DRS15NLW
NEMA 5-20, 20A 125V 	Black	CRS20BLKTR	CBRS20BLKTR	DRS20BLKTR	—
	Brown	CRS20TR	CBRS20TR	DRS20TR	—
	Gray	CRS20GRYTR	CBRS20GRYTR	DRS20GRYTR	—
	Ivory	CRS20ITR	CBRS20ITR	DRS20ITR	—
	Light Almond White	CRS20LATR CRS20WTR	CBRS20LATR CBRS20WTR	DRS20LATR DRS20WTR	—

Note: See page R-6 for tamper-resistant and weather resistant descriptions.
See page A-11 for dimensional art.
*Fed. Spec. Listed.

15A and 20A 125V Self-Grounding Weather Resistant and Tamper-Resistant Receptacles





Wiring		Back and Side Wired	
Rating	Color	Standard	Decorator
NEMA 5-15, 15A 125V 	Black	CBRS15BLKWTR	DRS15BLKWTR
	Brown	CBRS15WRTR	DRS15WRTR
	Gray	CBRS15GRYWRTR	DRS15GRYWRTR
	Ivory	CBRS15IWRTR	DRS15IWRTR
	Light Almond White	CBRS15LAWRTR CBRS15WWRTR	DRS15LAWRTR DRS15WWRTR
NEMA 5-20, 20A 125V 	Black	CBRS20BLKWTR	DRS20BLKWTR
	Brown	CBRS20WRTR	DRS20WRTR
	Gray	CBRS20GRYWRTR	DRS20GRYWRTR
	Ivory	CBRS20IWRTR	DRS20IWRTR
	Light Almond White	CBRS20LAWRTR CBRS20WWRTR	DRS20LAWRTR DRS20WWRTR

Note: See page R-6 for tamper-resistant and weather resistant descriptions.
See page A-11 for dimensional art.

15A and 20A 125V Self-Grounding Weather Resistant Receptacles



Wiring		Back and Side Wired
Rating	Color	Standard*
NEMA 5-15, 15A 125V 	Black	CBRS15BLKWTR
	Brown	CBRS15WRTR
	Gray	CBRS15GRYWRTR
	Ivory	CBRS15IWRTR
	Light Almond White	CBRS15LAWRTR CBRS15WWRTR
NEMA 5-20, 20A 125V 	Black	CBRS20BLKWTR
	Brown	CBRS20WRTR
	Gray	CBRS20GRYWRTR
	Ivory	CBRS20IWRTR
	Light Almond White	CBRS20LAWRTR CBRS20WWRTR

Note: *Fed. Spec. Listed.