

Toggle AC Motor Controllers Suitable as Disconnects (See Section G for Product Features)



Description	Amp	Phase	Poles	HP Ratings				Catalog Number
				120V AC	240V AC	480V AC	600V AC	
Toggle switch	30	1	2	2	5	10	15	30002D
Short toggle switch	30	1	2	2	5	10	15	30002DS
Toggle switch	30	3	3	3	7.5	15	20	30003D
Short toggle switch	30	3	3	3	7.5	15	20	30003DS
Toggle switch	40	1	2	2	5	10	15	40002D*
Toggle switch	40	3	3	3	7.5	15	25	40003D
Toggle switch	50	1	2	2	5	10	15	50002D
Toggle switch	50	3	3	3	7.5	15	25	50003D
Toggle switch	60	1	2	–	10	15	20	60002D
Toggle switch	60	3	3	–	10	25	30	60003D
Toggle switch – front wire	60	1	2	–	10	15	20	60002FWD
Toggle switch – front wire	60	3	3	–	10	25	30	60003FWD
Toggle switch	85	1	2	–	10	15	20	85002D
Toggle switch	85	3	3	–	10	25	40	85003D

Note: *For motor controller only, use catalog number 4002.

Rotary AC Manual Motor Controllers Suitable as Disconnects (See Section G for Product Features)




Description	Amp	Phase	Poles	HP Ratings				Catalog Number
				120V AC	240V AC	480V AC	600V AC	
Rotary switch	30	1	2	2	5	10	15	66032D
Rotary switch	30	3	3	3	7.5	15	20	66033D
Rotary switch	40	1	2	2	5	10	15	66042D
Rotary switch	40	3	3	3	7.5	15	25	66043D
Rotary switch	60	1	2	–	10	15	20	66062D
Rotary switch	60	3	3	–	10	25	30	66063D

Toggle and Rotary Enclosed Switches Suitable as Disconnects (See Section G for Product Features)



Description	Amp	Phase	Poles	HP Ratings				Catalog Number
				120V AC	240V AC	480V AC	600V AC	
NEMA 1 aluminum – toggle	30	1	2	2	5	10	15	30102D
NEMA 1 aluminum – toggle	30	3	3	3	7.5	15	20	30103D
NEMA 3/3R non-metallic	30	1	2	2	5	10	15	30322D
NEMA 3/3R non-metallic	30	3	3	3	7.5	15	20	30323D
NEMA 3R die cast aluminum	30	1	2	2	5	10	15	30312D
NEMA 3R die cast aluminum	30	3	3	3	7.5	15	20	30313D
NEMA 3R aluminum	30	1	2	2	5	10	15	30302D
NEMA 3R aluminum	30	3	3	3	7.5	15	20	30303D
NEMA 3R aluminum	60	1	2	–	10	15	20	60302D
NEMA 3R aluminum	60	3	3	–	10	25	30	60303D
NEMA 4X stainless steel	30	3	3	3	7.5	15	20	664S33D
NEMA 4X stainless steel	60	3	3	–	10	25	30	664S63D
NEMA 4X rotary motor controller	30	3	3	3	7.5	15	20	664X33D
NEMA 4X rotary motor controller	40	3	3	3	7.5	15	20	664X43D
NEMA 4X rotary motor controller	60	3	3	–	10	25	30	664X63D

Accessories (See Section G for Product Features)



Description	Catalog Number
Finger guards, red, for use with 30, 40 and 50 amp switches (set of 2)	30003FG
Handle kit for rotary switch, includes handle, shaft, mounting brackets and required screws	6610MK
Weatherproofing kit for rotary switch, includes 4 seals, neoprene bushing and 3 "O" rings	664XWP
Auxiliary contact NO/NC, includes 1 contact for use with push-on terminals	660AC
Mounting feet for NEMA 4X enclosure	664XFT
Neutral buss connector for NEMA 4X enclosure	6603N