

netSELECT® Voice/Data Jacks provide for a wide range of applications ranging from high performance data demands of Cat. 6 and Cat. 5e, to simple voice grade USOC jacks.

- Easy to terminate angled wiring towers
- Meets FCC part 68
- Meets and exceeds ANSI/TIA - Category 6 and Category 5e standards
- UL Listed and CSA Certified



netSELECT® Category 6, 5e and USOC Jacks

Color	Modular Snap Fit Cat. 6 Jack (single)	Modular Snap Fit Cat. 6 Jack (25 pack)	Modular Snap Fit Cat. 5e Jack (single)	Modular Snap Fit Cat. 5e Jack (25 pack)	Modular Snap Fit USOC Jack
Black	NSJ6BK	NSJ6BK25	NSJ5EBK	NSJ5EBK25	NSJUBK
Blue	NSJ6B	NSJ6B25	NSJ5EB	NSJ5EB25	NSJUB
Gray	NSJ6GY	NSJ6GY25	NSJ5EGY	NSJ5EGY25	NSJUGY
Green	NSJ6GN	NSJ6GN25	NSJ5EGN	NSJ5EGN25	NSJUGN
Ivory	NSJ6I	NSJ6I25	NSJ5EI	NSJ5EI25	NSJUI
Light Almond	NSJ6LA	NSJ6LA25	NSJ5ELA	NSJ5ELA25	NSJULA
Orange	NSJ6OR	NSJ6OR25	NSJ5EOR	NSJ5EOR25	NSJUOR
Red	NSJ6R	NSJ6R25	NSJ5ER	NSJ5ER25	NSJUR
White	NSJ6W	NSJ6W25	NSJ5EW	NSJ5EW25	NSJUW
Yellow	NSJ6Y	NSJ6Y25	NSJ5EY	NSJ5EY25	NSJUY



RJ-45 Couplers

Female to Female Couplers

Housing Color	Category 6, Pass-Thru	Category 5e, Pass-Thru	Category 5e, Cross Over 10/100BASE-T
Black	SFC6BK	SFC5EBK	-
Gray	-	-	SF5ECOY
White	SFC6W	SFC5EW	-

HDMI 1.4 Connectors for IMB and ISFB Series Blanks

Color	HDMI Keystone Feed-Thru	HDMI Feed-Thru Coupler	HDMI Feed-Thru 3-Inch Tail
	SFHC14BK SFHC14W	HDMIC14	HDMIT14
		-	-

USB Connectors

Pass-Thru, Female to Female Couplers

Housing Color	USB 3.0, A to A	USB 3.0, A to B	USB 2.0, A to A	USB 2.0, A to B
Black	SFUSBAA3BK	SFUSBAB3BK	-	-
Blue	-	-	SFUSBAAB	SFUSBABB
Office White	-	-	SFUSBAAOW	SFUSBABOW
White	-	-	SFUSBAAW	SFUSBABW



HDMI Non-Active Horizontal Patch Cords

Black, Non-Plenum, #24 AWG, HDMI 4K

Length (ft)	HDMI Device Patch Cords	Length (ft)	In-Wall Cords, (Male with Screw to Male with Screw)
3	HDPC03BK	10	HDH10BK
6	HDPC06BK	15	HDH15BK
		20	HDH20BK
		25	HDH25BK
		30	HDH30BK

Note: See page R-12 for modules and frames.