

### Toggle AC Motor Controllers Suitable as Disconnects (See Section G for Product Features)



Description	Amp	Phase	Poles	HP Ratings				Catalog Number
				120V AC	240V AC	480V AC	600V AC	
Toggle switch	30	1	2	2	5	10	15	<b>30002D</b>
Short toggle switch	30	1	2	2	5	10	15	<b>30002DS</b>
Toggle switch	30	3	3	3	7.5	15	20	<b>30003D</b>
Short toggle switch	30	3	3	3	7.5	15	20	<b>30003DS</b>
Toggle switch	40	1	2	2	5	10	15	<b>40002D*</b>
Toggle switch	40	3	3	3	7.5	15	25	<b>40003D</b>
Toggle switch	50	1	2	2	5	10	15	<b>50002D</b>
Toggle switch	50	3	3	3	7.5	15	25	<b>50003D</b>
Toggle switch	60	1	2	—	10	15	20	<b>60002D</b>
Toggle switch	60	3	3	—	10	25	30	<b>60003D</b>
Toggle switch – front wire	60	1	2	—	10	15	20	<b>60002FWD</b>
Toggle switch – front wire	60	3	3	—	10	25	30	<b>60003FWD</b>
Toggle switch	85	1	2	—	10	15	20	<b>85002D</b>
Toggle switch	85	3	3	—	10	25	40	<b>85003D</b>

Note: \*For motor controller only, use catalog number 4002.

### Rotary AC Manual Motor Controllers Suitable as Disconnects (See Section G for Product Features)



Description	Amp	Phase	Poles	HP Ratings				Catalog Number
				120V AC	240V AC	480V AC	600V AC	
Rotary switch	30	1	2	2	5	10	15	<b>66032D</b>
Rotary switch	30	3	3	3	7.5	15	20	<b>66033D</b>
Rotary switch	40	1	2	2	5	10	15	<b>66042D</b>
Rotary switch	40	3	3	3	7.5	15	25	<b>66043D</b>
Rotary switch	60	1	2	—	10	15	20	<b>66062D</b>
Rotary switch	60	3	3	—	10	25	30	<b>66063D</b>

### Toggle and Rotary Enclosed Switches Suitable as Disconnects (See Section G for Product Features)



Description	Amp	Phase	Poles	HP Ratings				Catalog Number
				120V AC	240V AC	480V AC	600V AC	
NEMA 1 aluminum – toggle	30	1	2	2	5	10	15	<b>30102D</b>
NEMA 1 aluminum – toggle	30	3	3	3	7.5	15	20	<b>30103D</b>
NEMA 3/3R non-metallic	30	1	2	2	5	10	15	<b>30322D</b>
NEMA 3/3R non-metallic	30	3	3	3	7.5	15	20	<b>30323D</b>
NEMA 3R die cast aluminum	30	1	2	2	5	10	15	<b>30312D</b>
NEMA 3R die cast aluminum	30	3	3	3	7.5	15	20	<b>30313D</b>
NEMA 3R aluminum	30	1	2	2	5	10	15	<b>30302D</b>
NEMA 3R aluminum	30	3	3	3	7.5	15	20	<b>30303D</b>
NEMA 3R aluminum	60	1	2	—	10	15	20	<b>60302D</b>
NEMA 3R aluminum	60	3	3	—	10	25	30	<b>60303D</b>
NEMA 4X stainless steel	30	3	3	3	7.5	15	20	<b>664S33D</b>
NEMA 4X stainless steel	60	3	3	—	10	25	30	<b>664S63D</b>
NEMA 4X rotary motor controller	30	3	3	3	7.5	15	20	<b>664X33D</b>
NEMA 4X rotary motor controller	40	3	3	3	7.5	15	20	<b>664X43D</b>
NEMA 4X rotary motor controller	60	3	3	—	10	25	30	<b>664X63D</b>

### Accessories (See Section G for Product Features)



Description	Catalog Number
Finger guards, red, for use with 30, 40 and 50 amp switches (set of 2)	<b>30003FG</b>
Handle kit for rotary switch, includes handle, shaft, mounting brackets and required screws	<b>6610MK</b>
Weatherproofing kit for rotary switch, includes 4 seals, neoprene bushing and 3 "O" rings	<b>664XWP</b>
Auxiliary contact NO/NC, includes 1 contact for use with push-on terminals	<b>660AC</b>
Mounting feet for NEMA 4X enclosure	<b>664XFT</b>
Neutral buss connector for NEMA 4X enclosure	<b>6603N</b>