

Network Wiring

In-Wall AV Delivery

netSELECT®



- High density delivery of power, data and AV
- Stud or sheetrock mounting flexibility
- Steel construction for residential MDU and commercial applications
- Easily reconfigured to adapt to new applications



FPTV Connection Enclosure Inches (mm)

Description	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Catalog Number
2-gang in-wall enclosure	7.92" (201)	8.16" (207)	3.37" (86)	NSAV62M
4-gang in-wall enclosure	7.92" (201)	14.80" (376)	3.37" (86)	NSAV124M
Steel cover for NSAV62M	7.2" (183)	7.2" (183)	0.05" (1)	NSAV6C
Steel cover for NSAV124M	7.2" (183)	13.80" (351)	0.05" (1)	NSAV12C
Block wall adapter				NSAV6BW
New work stud brackets				NSAV6NW

Power Kits

Description	Color	Catalog Number
Standard power kit, includes wallplate, box and 15A tamper-resistant outlet	White	NSOKPTR
Surge protected power kit, includes wallplate, box and surge protected outlet	Blue	NSOKPS



HDMI Frames

Description	Color	1-Gang, 1-Port	1-Gang, 2-Port
HDMI, decorator frame, female to female	Black	NS801BK	NS802BK
	Gray	NS801GY	NS802GY
	Ivory	NS801I	NS802I
	Light Almond	NS801LA	NS802LA
	White	NS801W	NS802W


Recessed Receptacles

Color	15A 125V, Tamper-Resistant Duplex Receptacle		
	1-Gang	2-Gang with Feed-Through	2-Gang with Snap Fit
Ivory	RR1510I	RR1512I	RR1514I
Light Almond	RR1510LA	RR1512LA	RR1514LA
White	RR1510W	RR1512W	RR1514W

Feed-Through Plates

Color	1-Gang	2-Gang
Ivory	NSAV11*	NSAV21*
White	NSAV1W*	NSAV2W*

Note: *Not UL Listed.



Two and Three Gangable AV Wallboxes Inches (mm)

Box	Dimensions			Top Knockouts	Bottom Knockouts	Back Knockouts	Catalog Number
	Height	Width	Depth				
2-Gang, 2" KO, 54 in ³ capacity	4.21" (107)	4.06" (103)	4.0" (102)	(2) 1/2" (2) 1/2" - 3/4" TKO*	(1) 1", 1 1/4", 1 1/2" and 2"	(2) 1/2" - 3/4" TKO	HBL985
3-Gang, 2" KO, 79 in ³ capacity	4.21" (107)	5.87" (149)	4.0" (102)	(3) 1/2" (3) 1/2" - 3/4" TKO*	(1) 1/2", (1) 1/2" - 3/4" TKO* (1) 1", 1 1/4", 1 1/2" and 2"	(3) 1/2" - 3/4" TKO	HBL986

Note: *TKO (Tangential Knockout).

Wallbox

Description	Color	Catalog Number
2-Gang, nail-on box, thermoplastic	Blue	RR1500

Low Voltage AV Wallbox Partitions

Compatible With	Description	Quantity	Catalog Number
HBL985 and HBL986	Solid divider	1	HBL989
	With pass-thru capability	1	HBL989AVD