YAB6CCG15, Compression Terminal, #6 AWG, M8 Stud

By Burndy
Catalog # YAB6CCG15

Cast Lug; AWG#6; M8 STUD.

Application

Wire Termination

General

Catalog Number	YAB6CCG15
Color Code	Blue
Connector Type	LONG BARREL
Die Index	7
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810468326
UPC 12 Digit	7818104683266

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - D inch	0.88 in
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.57 in
Dimension - N inch	0.44 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.88 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size fraction	5/16
Dimension - Z (inch)	0.44 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	25

Product Assets

3D Models - YAB6CCG15_MODEL-STEP
3D Models - YAB6CCG15_MODEL-PDF
3D Models - YAB6CCG15_MODEL-IGES
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - 10087570
Specifications - YAB6CCG15
Video - HYDENT Compression Terminal Overview Video

©2024 Hubbell Incorporated. All rights reserved