



# Wallplates and Covers

## Combination Wallplates



### Combination Wallplates, 2-Gang

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
2-Gang, 1-Toggle, 1-Single Receptacle 1.40 in. (35.6) Hole 	Black Brown Gray Ivory White	<b>NP17BK</b> <b>NP17</b> <b>NP17GY</b> <b>NP17I</b> <b>NP17W</b>	- - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① <b>SS17</b> -
2-Gang, 1-Toggle, 1-Blank Box Mount 	Black Brown Gray Ivory Light Almond White	<b>NP113BK</b> <b>NP113</b> <b>NP113GY</b> <b>NP113I</b> <b>NP113LA</b> <b>NP113W</b>	- <b>NPJ113</b> - <b>NPJ113I</b> - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① <b>SS113</b> -
2-Gang, 1-Toggle, 1-Blank Strap Mount 	Black Gray Ivory White	- - - -	- - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① <b>SS114</b> -
2-Gang, 1-Blank, 1-Duplex Box Mount 	Black Brown Gray Ivory Light Almond White	<b>NP138BK</b> <b>NP138</b> <b>NP138GY</b> <b>NP138I</b> <b>NP138LA</b> <b>NP138W</b>	- <b>NPJ138</b> - <b>NPJ138I</b> - <b>NPJ138W</b>	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① <b>SS138</b> -
2-Gang, 1-Blank, 1-Duplex Strap Mount 	Black Gray Ivory White	- - - -	- - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① <b>SS148</b> -
2-Gang, 1-Blank, 1-Decorator Box Mount 	Black Brown Gray Ivory Light Almond White	<b>NP1326BK</b> <b>NP1326</b> <b>NP1326GY</b> <b>NP1326I</b> <b>NP1326LA</b> <b>NP1326W</b>	<b>NPJ1326BK</b> <b>NPJ1326</b> <b>NPJ1326GY</b> <b>NPJ1326I</b> <b>NPJ1326LA</b> <b>NPJ1326W</b>	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① <b>SS1426*</b> -
2-Gang, 1-Telephone, 1-Blank, 406 in. (10.3) Hole, Strap Mount 	Black Brown Gray Ivory White	<b>NP1214BK</b> <b>NP1214</b> <b>NP1214GY</b> <b>NP1214I</b> <b>NP1214W</b>	- - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	- - - - - -
2-Gang, 1-Single Receptacle, 1-Blank 1.40 in. (35.6) Hole, Strap Mount 	Black Brown Gray Ivory White	<b>NP147BK</b> <b>NP147</b> <b>NP147GY</b> <b>NP147I</b> <b>NP147W</b>	- - - - -	Aluminum Brass Brass Plated Chrome S/S 302/304 S/S 430	① ① ① ① ① -

Note: All nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate, see pages Q-28-Q30. Consult custom wallplates section for additional openings and combinations.

\*Strap Mount.