




# DISTRIBUTION TOOLS SERIES GP FARGO CONNECTOR WRENCHES

TOOLS  
GP WRENCHES

- Design optimized for lineman use - handle separates both ends. (GP201-204 & GP216 are 1 piece style - see note)
- Specially constructed for proper and fast installation of mechanical connectors in utility distribution applications

Sturdy polypropylene handle provides protection from incidental end-to-end or energized line contact (all models except as noted).

Nine available wrench heads.



## Fargo Available Wrench Combinations:

CATALOG NUMBER	"A" END DESCRIPTION	FIGURE	C INCHES (MM)	"B" END DESCRIPTION	FIGURE	C INCHES (MM)	L APPROX. INCHES (MM)	WT. LB. (KG)
GP201*	3/8" Ratchet	1	one piece	9/16" Ratchet	1	one piece	6.75 (171.79)	0.75 (0.34)
GP203*	9/16" Ratchet	1	one piece	3/4" Ratchet	1	one piece	6.25 (159.06)	0.75 (0.34)
GP2031*	1/2" Ratchet	1	one piece	9/16" Ratchet	1	one piece	6.75 (171.79)	0.75 (0.34)
GP204*	11/16" Ratchet	1	one piece	15/16" Ratchet	1	one piece	9.25 (235.41)	0.75 (0.34)
GP216*	11/16" Ratchet	1	one piece	15/16" Ratchet	1	one piece	9.25 (235.41)	0.75 (0.34)
GP209	3/8" Allen Ratchet	4	1.21 (30.79)	Eye Loop	9	1.00 (25.45)	7.50 (190.88)	0.75 (0.34)
GP2090P	3/8" Allen Ratchet	4	1.21 (30.79)	Penta Socket	6	2.00 (50.90)	8.75 (222.69)	1.00 (0.45)
GP2090P4	3/8" Allen Ratchet	4	1.71 (43.52)	Penta Socket	6	2.00 (50.90)	8.75 (222.69)	1.00 (0.45)
GP2090P90	3/8" Allen Ratchet	4	1.21 (30.79)	90° Penta Socket	7	2.50 (63.63)	9.25 (235.41)	1.00 (0.45)
GP2091P	Penta Socket	6	1.91 (48.61)	Eye Loop	9	1.00 (25.45)	7.50 (190.88)	0.75 (0.34)
GP2091P90	90 Penta Socket	7	2.37 (60.32)	Eye Loop	9	1.00 (25.45)	8.00 (203.60)	0.75 (0.34)
GP2092M	3/8" Allen Ratchet	4	1.21 (30.79)	3/8" Allen Bar	3	1.25 (31.81)	8.00 (203.60)	0.75 (0.34)
GP2093	5/16" Allen Ratchet	4	1.46 (37.16)	Eye Loop	9	1.00 (25.45)	7.75 (197.24)	0.75 (0.34)
GP2093P	5/16" Allen Ratchet	4	1.46 (37.16)	Penta Socket	6	2.00 (50.90)	9.00 (229.05)	1.00 (0.45)
GP2093P90	5/16" Allen Ratchet	4	1.46 (37.16)	90° Penta Socket	7	2.50 (63.63)	9.25 (235.41)	1.00 (0.45)
GP209375P90	5/16" Allen Ratchet	4	0.75 (19.09)	90° Penta Socket	7	2.50 (63.63)	9.25 (235.41)	1.00 (0.45)

\* These wrenches do not have polypropylene handle.



# DISTRIBUTION TOOLS SERIES GP FARGO CONNECTOR WRENCHES (CONTINUED)

TOOLS
<b>GP WRENCHES</b>

### Fargo Available Wrench Combinations:

CATALOG NUMBER	A END DESCRIPTION	FIGURE	C INCHES (MM)	D END DESCRIPTION	FIGURE	INCHES (MM)	L APPROX. INCHES (MM)	WT. LB. (KG)
GP210	3/16" Allen Bar	3	1.25 (31.81)	Eye Loop	9	1.00 (25.45)	6.75 (171.79)	0.50 (0.23)
GP2101	1/4" Allen Bar	3	1.88 (47.85)	Eye Loop	9	1.00 (25.45)	7.38 (187.82)	0.50 (0.23)
GP211	3/8" Allen Bar	3	1.25 (31.81)	Eye Loop	9	1.00 (25.45)	6.75 (171.79)	0.50 (0.23)
GP212	5/16" Allen Bar	3	1.25 (31.81)	Eye Loop	9	1.00 (25.45)	6.75 (171.79)	0.50 (0.23)
GP221	3/8" Ratchet	1	2.25 (57.26)	9/16" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2210	3/8" Ratchet	1	2.25 (57.26)	7/16" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2212	1/2" Ratchet	1	2.25 (57.26)	9/16" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2213	5/16" Ratchet	1	2.00 (50.90)	3/8" Ratchet	1	2.00 (50.90)	8.50 (216.33)	0.75 (0.34)
GP2213AR	3/8" Allen Ratchet	4	1.21 (30.79)	5/16" Allen Ratchet	4	1.21 (30.79)	9.00 (229.05)	0.75 (0.34)
GP2214	3/8" Ratchet	1	2.00 (50.90)	1/2" Ratchet	1	2.00 (50.90)	8.50 (216.33)	0.75 (0.34)
GP2215P	3/8" Reversible Ratchet	2	2.25 (57.26)	Penta Socket	6	2.00 (50.90)	8.75 (222.69)	1.00 (0.45)
GP223	9/16" Ratchet	1	2.25 (57.26)	3/4" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2231	9/16" Ratchet	1	2.25 (57.26)	11/16" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2232	3/4" Ratchet	1	2.25 (57.26)	11/16" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2233	9/16" Ratchet	1	2.25 (57.26)	5/8" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2234	1/2" Ratchet	1	2.25 (57.26)	5/8" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2235	5/8" Ratchet	1	2.25 (57.26)	11/16" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2236	5/8" Ratchet	1	2.25 (57.26)	13/16" Ratchet	1	2.75 (69.99)	9.50 (241.78)	0.75 (0.34)
GP2237	5/8" Ratchet	1	2.25 (57.26)	3/4" Ratchet	1	2.25 (57.26)	9.00 (229.05)	0.75 (0.34)
GP2238	3/4" Ratchet	1	2.25 (57.26)	13/16" Ratchet	1	2.75 (69.99)	9.50 (241.78)	0.75 (0.34)
GP224	3/4" Ratchet	1	2.25 (57.26)	7/8" Ratchet	1	2.75 (69.99)	9.50 (241.78)	1.00 (0.45)
GP2240	13/16" Ratchet	1	2.75 (69.99)	7/8" Ratchet	1	2.75 (69.99)	10.00 (254.50)	1.00 (0.45)
GP2241P90	13/16" Ratchet	1	2.75 (69.99)	90° Penta Socket	7	2.50 (63.63)	9.75 (248.14)	1.00 (0.45)
GP2242	11/16" Ratchet	1	2.25 (57.26)	15/16" Ratchet	1	2.75 (69.99)	9.50 (241.78)	1.00 (0.45)
GP2243	13/16" Ratchet	1	2.75 (69.99)	15/16" Ratchet	1	2.75 (69.99)	10.00 (254.50)	1.00 (0.45)
GP2245	7/8" Ratchet	1	2.75 (69.99)	15/16" Ratchet	1	2.75 (69.99)	10.00 (254.50)	1.00 (0.45)
GP239	5/16" Rev. Allen Ratchet	5	1.00 (25.45)	5/16" Rev. Allen Ratchet	5	1.00 (25.45)	9.00 (229.05)	1.00 (0.45)
GP240	5/16" Rev. Allen Ratchet	5	1.50 (38.18)	3/8" Rev. Allen Ratchet	5	1.38 (35.12)	9.00 (229.05)	1.00 (0.45)
GP240P1	3/8" Rev. Allen Ratchet	5	1.00 (25.45)	Penta Socket	6	2.00 (50.90)	8.75 (222.69)	1.00 (0.45)
GP241P	5/16" Rev. Allen Ratchet	5	1.50 (38.18)	Penta Socket	6	2.00 (50.90)	8.75 (222.69)	1.00 (0.45)
GP241P1	5/16" Rev. Allen Ratchet	5	2.00 (50.90)	Penta Socket	6	2.00 (50.90)	8.75 (222.69)	1.00 (0.45)
GP241P2	5/16" Rev. Allen Ratchet	5	1.00 (25.45)	Penta Socket	6	2.00 (50.90)	8.75 (222.69)	1.00 (0.45)
GP241P3	5/16" Rev. Allen Ratchet	5	2.50 (63.63)	Penta Socket	6	2.00 (50.90)	8.75 (222.69)	1.00 (0.45)
GP241P90	5/16" Rev. Allen Ratchet	5	1.50 (38.18)	90° Penta Socket	7	2.50 (63.63)	9.25 (235.41)	1.00 (0.45)
GP241PS58	5/16" Rev. Allen Ratchet	5	0.63 (15.91)	Penta Socket	6	2.00 (50.90)	8.75 (222.69)	1.00 (0.45)
GP241S	5/16" Rev. Allen Ratchet	5	1.50 (38.18)	Eye Loop	9	1.00 (25.45)	7.75 (197.24)	0.75 (0.34)
GP241S2	5/16" Rev. Allen Ratchet	5	1.00 (25.45)	Eye Loop	9	1.00 (25.45)	9.00 (229.00)	0.75 (0.34)
GP241S3GP	3/8" Rev. Allen Ratchet	5	1.00 (25.45)	Eye Loop	9	1.00 (25.45)	9.00 (229.00)	0.75 (0.34)
GP241S58	5/16" Rev. Allen Ratchet	5	0.63 (15.91)	Eye Loop	9	1.00 (25.45)	7.75 (197.24)	0.75 (0.34)
GP242P	5/16" Rev. Allen Ratchet	5	1.75 (44.54)	90° Penta Rev. Ratchet	8	2.75 (69.99)	9.00 (229.00)	1.00 (0.45)
GP242P1	3/8" Rev. Allen Ratchet	5	1.38 (35.12)	90° Penta Rev. Ratchet	8	2.75 (69.99)	9.00 (229.00)	1.00 (0.45)
GP242P2	5/16" Rev. Allen Ratchet	5	2.00 (50.90)	90° Penta Rev. Ratchet	8	2.75 (69.99)	9.00 (229.00)	1.00 (0.45)
GP243P	5/16" Rev. Allen Ratchet	5	1.00 (25.45)	90° Penta Socket	7	2.50 (63.63)	9.25 (235.41)	1.00 (0.45)
GP516A	5/16" Rev. Allen Ratchet	5	2.5 (63.5)	5/16" Allen Bar	3	2.36 (59.9)	9.11 (231.39)	0.50 (0.23)

DG  
2