



GENERAL USE - GROUNDING AND BONDING VISE TYPE BRONZE


For Bonding Ribbon, Braid and Tape

Bonding ribbon or braid to bonding ribbon, braid, conductor, or bus and tape to messenger.

Product Data & Conductor Size

CATALOG NUMBER	BONDING RIBBON OR BRAID		APPROX. DIMENSIONS INCHES					WT LB (KG)
	CONNECT	TO	A (MM)	B (MM)	C (MM)	BOLT		
						DIA.	WRENCH	
GC164	Ribbon	Ribbon, Braid, #6	1	5/8	1	1/4	3/8	.12
GC164P [†]	or Braid	or Bus	(25.45)	(15.90)	(25.45)	(6.36)	(10)	(.05)

[†] Plated Bronze



GC164


For Ground Rods

Product Data & Conductor Size

CATALOG NUMBER	RANGE		APPROX. DIMENSIONS INCHES					WT LB (KG)
	ROD DIA. INCHES (MM)	CONDUCTOR	A (MM)	B (MM)	C (MM)	BOLT		
						DIA.	WRENCH	
GC268 [†]	1/4 - 5/8 (6.36-15.90)	6-1/0	2 (50.80)	1 (25.45)	1-3/8 (35.00)	3/8 (9.54)	9/16 (14)	.43 (.19)

* Torque head bolts available for tamperproof, removeable connection.

[†]Complies with UL-467 and ETL listed



GC268


For Lashing Wire

Connect small diameter lashing wires to messengers.

Product Data & Conductor Size

CATALOG NUMBER	MESSENGER DIAMETER RANGE	LASHING WIRE	APPROX. DIMENSIONS INCHES					WT LB (KG)
	CONNECT (MM)		TO	A (MM)	B (MM)	C (MM)	BOLT	
		DIA.					WRENCH	
GC166	.245" - .500"	All Sizes	1-1/2	7/8	1	1/4	3/8	.16
GC166P	(6.23-12.73)		(38.18)	(22.26)	(25.45)	(6.36)	(10)	(.07)

Suffix P- Plated Bronze



GC166

For Guy Strand

Aluminum bodied connectors for connecting galvanized or aluminum clad strand to copper conductors. Vise Type Parallel Connector.


Product Data & Conductor Size

CATALOG NUMBER	STRAND RANGE (IN.) (MM)	CONDUCTOR RANGE	APPROX. DIMENSIONS INCHES			WT LB (KG)
			A (MM)	B (MM)	C (MM)	
GA9003L**	1/4 (6.36)	4-8	7/8 (22.26)	1-1/4 (31.81)	1-3/4 (44.54)	.17 (.08)
GA9002L**	1/4 - 3/8 (6.36-9.54)	4-8	1-1/8 (28.63)	1-7/8 (47.72)	2-1/8 (54.08)	.23 (.10)
PARALLEL GROOVE TYPE						
LC52AXB***	1/4 - 3/8	2/0 - 8	2-3/8	1-5/8	1-3/8	.20
LC522AXB***	(6.36-9.54)		(60.44)	(41.36)	(35.00)	(.09)

* Inhibitor Protected and Individually Packaged - Standard

[†] Bimetallic Liner on Tap Side - Copper

**RUS Listed



LC50 Series