


OTHER DISTRIBUTION ONE PIECE WILDLIFE PROTECTOR

POLYPROPYLENE
GS Series

- Designed to provide protection for equipment bushing from accidental contact by squirrels, birds or other wildlife.
- Hinged construction for easy installation or retrofit on a variety of bushing insulators. Equipment tap wire does not have to be disconnected during installation.
- Flexible “fingers” on cable entry ports close around tap conductor and cover unused ports.
- Flexible “fingers” at base of protector provide a snug fit on various size bushings.

Material: Track resistant polypropylene stabilized with UV inhibitors for long term performance. Munsell gray color.

Note: GS565 is polyethylene with UV inhibitors. Munsell gray color.



GS555 Series

Figure 1



GS560 Series

Figure 2



GS565 Series Δ

Figure 3

Ordering Information

CATALOG NUMBER	FIGURE NO.	BUSHING ACCOMMODATED	LATCH TYPE	DIMENSIONS INCHES (MM)			WT. LB. (KG)
				D	H	NOMINAL INSULATOR SKIRT DIAMETER	
GS555H	1	Distribution and Transformer Bushings	2 Washboard-Peg	5.38 (136.92)	6.18 (156.97)	3.75" to 5.25" (95.44 to 133.61)	.28 (.13)
GS560H	2	Distribution and Transformer Bushings	2 Pinch Latches, One Top Clasp	4.88 (124.20)	10.59 (268.99)	3.75" to 4.75" (95.44 to 120.59)	.48 (.21)
GS565	3	Transformer Bushings	1 Piece Slot Design-Snap Joint	4.25 (108.16)	9.75 (248.14)	3.25" to 4.25" (82.71 to 108.16)	.40 (.18)

DI
1



OTHER DISTRIBUTION ONE PIECE WILDLIFE PROTECTOR

POLYPROPYLENE
GS




GS567

Figure 1



GS570

Figure 2



*Figure 3

Ordering Information

CATALOG NUMBER	FIGURE NO.	BUSHING ACCOMMODATED	DIMENSIONS INCHES (MM)			WT. LB. (KG)
			D	H	NOMINAL INSULATOR SKIRT DIAMETER	
GS567	1	Recloser, Regulator and Pot Head Bushings	6.38 (162.37)	10.50 (267.23)	5.00" to 6.25" (127.25 to 159.06)	.80 (.36)
GS570	2	Larger diameter bushings such as substation transformer & circuit breakers	8.12 (206.65)	13.75 (349.94)	6.75" to 8.00" (171.79 to 203.60)	1.21 (.55)
GS580	3	Covers Arrester to Line Connection (Lightning Arrester)	6.34 X 6.92 (161.35 X 176.11)	5.00 (127.25)	Fits up to 6" Diameter Arrester (153.70)	.40 (.18)

* See also GC207LA or LAT Lightning Arrester Terminals for bottom side of lightning arresters.

DI
2