



## Specifications

- Suitable for multimedia applications
- Compatible with HJ, XJ and SF style AV and fiber connectors

## UK-Style Wallplates and Modules

Description	Qty.	Catalog No.
Flat frame, 1-gang, 50 x 50mm	80-pack	<b>HBP50</b>
Flat frame, 2-gang, 100 x 50mm	50-pack	<b>HBP100</b>
Shuttered, unloaded, 50 x 25mm	125-pack	<b>HBM1</b>
Angled, shuttered, unloaded, 50 x 25mm	100-pack	<b>HBM1A</b>
Blanking plate, 50 x 25mm	50-pack	<b>HBM1B</b>



## UK LJ6C-Style Wallplates and Modules

Description	Qty.	Catalog No.
Shuttered, unloaded, 37 x 22.5mm (LJ6C)	100-pack	<b>HLJ6C</b>
Angled, shuttered, unloaded, 37 x 22.5mm (LJ6C)	100-pack	<b>HLJ6CA</b>
Flat frame, 1-gang, 2-port (LJ6C)	80-pack	<b>HLJ6CP2</b>
Flat frame, 2-gang, 4-port (LJ6C)	40-pack	<b>HLJ6CP4</b>



## French-Style Wallplates and Modules

Description	Qty.	Catalog No.
Single module, unloaded, 45 x 45mm	100-pack	<b>HFM1</b>
Dual module, unloaded, 45 x 45mm	100-pack	<b>HFM2</b>
Angled, dual module, unloaded, 45 x 45mm	100-pack	<b>HFM2A2</b>
Flat frame, 1-gang, 45 x 45mm	80-pack	<b>HFP45</b>
Flat frame, 1-gang, 90 x 45mm	25-pack	<b>HFP90</b>



## Asian-Style Wallplates

### Single Gang

	1-Port Plate, Unloaded	2-Port Plate, Unloaded	4-Port Plate
Flat Wall Plate, 86 x 86mm	<b>BPS11</b>	<b>BPS12</b>	–
Bevelled Wall Plate 86 x 86mm	<b>BPS11A</b>	<b>BPS12A</b>	–
Base Plate with Bevelled Frame, 86 x 86mm	<b>BPC11</b>	<b>BPC12</b>	<b>BPC14</b>
Base Plate w/ Bevelled Frame for Angled Jacks, 86 x 86mm	<b>BPC11A</b>	<b>BPC12A</b>	–



## Australian Clipsal® Style Module

Description	Qty.	Catalog No.
Keystone module	100-pack	<b>CKM100</b>

Clipsal® is a registered trademark of Clipsal Australia Pty Ltd. and/or Schneider Electric.