

Field Termination solutions for direct attach Modular Plug Terminated Links (MPTL).

Specifications

- Cable supported:
- F/FTP, S/FTP, F/UTP and UTP Cable jacket O.D. 0.236-0.315" (6-8mm)
- · Conductor: Solid: 22-26AWG
- Performance: ANSI/TIA-568-C.2 Category 6A and Category 6 channel
- Full 802.3bt (4PPoE) support, Type 3 and 4
- UL Plenum rated

NEXTSPEED® COBRA-LOCK™ Field Termination Plugs

Description	Catalog No.	
CAT6A Field Termination MPTL Plug	SP6A	
CAT6 Field Termination MPTL Plug	SP6	A start and a start an
CAT6A Field Termination MPTL Plug with 90° Cable Exit	SP6A90	
CAT6 Field Termination MPTL Plug with 90° Cable Exit	SP690	

NEXTSPEED [®] COBRA-LOCK [™] 6A Coupler		
Description	Catalog No.	
CAT6A MPTL Coupler	SC6A	11
CAT6A MPTL 18" Pre-Terminated Coupler Assembly	SCP6A	Vi-
Note: See page D09 for additional MTPL Assembly color and length options.		102



Jack Accessories

Jack Dust Covers, Compatible only with the HXJ **Xcelerator Jacks Only**

Description	Catalog No.	
Polypropylene, clear, 25-pack	HXJDC25	ليقتل
Note: Mounts within the ico	on slots located	

above the RJ45 opening. Cannot be used with SJ shielded jack series.



Secure-IT RJ-45 Port Blocker

Physically lock out access to individual RJ-45 ports with the Secure-IT Port Blocker. Compatible with any RJ-45 port, the blocker inserts easily and requires the supplied tool to remove.

Description	Catalog No.	19
Locking RJ-45 port blocker	RJ45PB50	and the second

Note: Fits any RJ-45 port. Note: See color chart on page BO2.

Jack Icons, Compatible with the HXJ Xcelerator **Jacks Only**

100-pack, snaps onto jack nose

Color	Blank Catalog No.	Computer Catalog No.	Telephone Catalog No.
Black	IBK100	IBK100C	IBK100T
Blue	IB100	IB100C	IB100T
Brown	IBN100	IBN100C	IBN100T
Gray	IGY100	IGY100C	IGY100T
Green	IGN100	IGN100C	IGN100T
lvory	IEI100	IEI100C	IEI100T
Orange	IOR100	IOR100C	IOR100T
Purple	IP100	IP100C	IP100T
Red	IR100	IR100C	IR100T
White	IW100	IW100C	IW100T
Yellow	IY100	IY100C	IY100T

Note: Cannot be used with SJ shielded jack series; custom icon numbering and labeling available; contact Customer Service for details.

Ο

