YDS361R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # YDS361R

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, Inner Sleeve: 5.25 IN L, Outer Sleeve: 25.63 IN L.

General

Catalog Number	YDS361R
Connector Type	Splice
Die Index - Element A	248
Die Index - Element B	327
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810821046
UPC 12 Digit	7818108210466

Dimensions

Dimension - Aluminum Sleeve Length inch	25.625 in
Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.5 in
Dimension - L Length Overall mm	645 mm
Dimension - Length Overall inch	25.38 in
Dimension - Outside Diameter inch	1.3 in
Dimension - Steel Sleeve Length inch	5.25 in

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	600

Product Assets

Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_YDS-R_LineArt
Sales Drawings - SA..039024-01
Specifications - YDS361R

©2024 Hubbell Incorporated. All rights reserved