YE28R60, Aluminum Terminal Plug

By Burndy
Catalog # YE28R60

Terminal Plug for AL and ACSR, 4/0 AL,4/0 ACSR, 9.5 in Length, Tin Plated, Pink, 840 or 249 or 11A Index.

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color

Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

General

Catalog Number	YE28R60
Color Code	Pink
Die Index	249;840;11A
EU RoHS Indicator	Yes
Material	Aluminum
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Trade Name	HYPLUG™
Type	YE-R
UPC	781810154304

Dimensions

Dimension - L Length Overall mm	241 mm
Dimension - Length Overall inch	9.50 in
Dimension - Outside Diameter inch	0.91 in
Dimension - P inch	6 in

Conductor Related

Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	4200

Product Assets

3D Models - YE28R60_MODEL-IGES
3D Models - YE28R60_MODEL-STEP
3D Models - YE28R60_MODEL-PDF
Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_YE28R60_Lineart
Sales Drawings - 50115710
Specifications - YE28R60

©2024 Hubbell Incorporated. All rights reserved