


- A** Conductor Bracket for Ladder  
**HGBTEBCBRKL10**
- B** 12ft Conductor with double lug  
**HGRKTD144DB**
- C** Ladder tray jumper  
**HGRKTD9D**
- D** Ladder to Conductor  
**HGRKTD60DB**
- E** Conductor with C-Tap to 76" Busbar  
**HGRKTD60C46**
- F** Conductor with C-Tap to 19" Busbar  
**HGRKTDA60C46**
- G** Conductor with C-Tap to 36" Busbar  
**HGRKTDB60C46**
- H** 76" x 3/4" Vertical Busbar  
**HBBBVR76KT**
- I** 19" Horizontal Busbar  
**HBBBHR19KT**
- J** 36" x 3/4" Vertical Busbar  
**HBBBVR36KT**
- K** 10" x 2" Wall Mounted Busbar  
**HBBB14210A**



## On-Rail Kits

Includes: 19" RGB busbar (HBBBHR19KT), mounting insulators, mounting hardware, lug mounting hardware, 60" 6AWG conductor (HGRKTX60D), VELCRO® Brand fastener straps, Penetrox™ AntiOxidant

Description	Material	Single Pack	10-Pack
On-rail mounted;	Copper	<b>HGRKTHC</b>	<b>HGRKTHC10</b>
19" rack grounding busbar	Tin-plated	<b>HGRKTHT</b>	<b>HGRKTHT10</b>



## In-Cabinet Kits

Includes: 36" RGB busbar (HBBBVR36KT), mounting insulators, mounting hardware, lug mounting hardware, 60" 6AWG conductor (HGRKTX60DB), VELCRO® Brand fastener straps, Penetrox™ AntiOxidant

Description	Material	Single Pack	10-Pack
In-cabinet mounted;	Copper	<b>HGRKTVC</b>	<b>HGRKTVC10</b>
36" rack grounding busbar	Tin-plated	<b>HGRKTVT</b>	<b>HGRKTVT10</b>



## Wall Mounted Busbars

Busbar kit includes: copper busbar with stainless steel brackets and insulators; (1) 6AWG lug; (1) 2AWG lug; (2) 2/OAWG lugs; (1) 4/OAWG lug; stainless steel lug mounting hardware; Penetrox™ AntiOxidant; ground label

Size	Catalog No.
2" x 10"	<b>HGRKTTGB10A</b>
4" x 16"	<b>HGRKTTMGB16H</b>



Note: VELCRO® is a registered trademark of Velcro Industries B.V. Penetrox™ is a trademark of Burndy Corporation.