YNA32R154N, ACSR, ACAR, Aluminum Terminal

By Burndy
Catalog # YNA32R154N

Compression terminal used for ACSR, ACAR and Stranded aluminum cable, 15 Degree connector.

General

Catalog Number	YNA32R154N
Connector Type	Terminal
Die Index	717
Material	Aluminum
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810491317
UPC 12 Digit	7818104913177

Dimensions

Dimension - L Length Overall mm	233 mm
Dimension - Length Overall inch	9.16 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.68 in

Conductor Related

Conductor - ACAR Str Size	400 (19)
Conductor - ACSR Str Size	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - AL Str Size	336.4;350

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Interactive Catalog - BURNDY Full-Line Digital Catalog
Specifications - YNA32R154N

©2024 Hubbell Incorporated. All rights reserved