# YNS451RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # YNS451RT

HYSPLICE™ Al Tube Jumper Loop Sleeve, For EHV, 840.2-927.2 kcmil(ACAR), 795-1000 kcmil(Al), 715.5-874.5 kcmil(ACSR), 230 kV, 10.60″ L, 725 Index.

## General

| | |
|---|---|
| Catalog Number | YNS451RT |
| Connector Type | Splice |
| Die Index | 725 |
| Material | Aluminum |
| Trade Name | HYSPLICE™ |
| UPC | 781810016497 |
| UPC 12 Digit | 7818100164977 |

## Dimensions

| | |
|---|---|
| Dimension - Diameter Max Size inch | 1.80 in |
| Dimension - L Length Overall mm | 269 mm |
| Dimension - Length Overall inch | 10.60 in |
| Dimension - Outside Diameter inch | 1.80 in |

## Conductor Related

| | |
|---|---|
| Conductor - ACAR Str Size Range | 715.5 KCMIL - 874.5 KCMIL |
| Conductor - ACSR Str Size | 715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil |
| Conductor - ACSR Str Size Range | 715.5 (26/7) Starling kcmil-795 (54/7) Condor kcmil |
| Conductor - AL Str Size | 795 KCMIL - 1000 KCMIL |
| Conductor - AL Str Size Range | 795 KCMIL - 1000 KCMIL |

## Certifications And Compliance

| | |
|---|---|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

## Logistics

| | |
|---|---|
| Carton Quantity | 6 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 1008 |

## Product Assets

Catalogs - BURNDY Master Catalog - Section I - Transmission
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_YNS-RT_LINEART_BW
Sales Drawings - SD058033-01
Specifications - YNS451RT


©2024 Hubbell Incorporated. All rights reserved