YNS52RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # YNS52RT

HYSPLICE™, ACCOM: 1113 54-19 STR - 135 kcmil ACSR 1277-1280 kcmil ACSR 1351.5-1510 kcmil AL INDEX: 728 T&B 189.

General

Catalog Number	YNS52RT
Connector Type	Splice
Die Index	728
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810180631
UPC 12 Digit	7818101806311

Dimensions

Dimension - Diameter Max Size inch	2.25 in
Dimension - L Length Overall mm	411 mm
Dimension - Length Overall inch	16.20 in
Dimension - Outside Diameter inch	2.25 in

Conductor Related

Conductor - ACAR Str Size Range	1277 KCMIL - 1280 KCMIL
Conductor - ACSR Str Size	1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil;1351.5 (54/19) Martin kcmil
Conductor - ACSR Str Size Range	1113 (54/19) Finch kcmil-1351.5 (54/19) Martin kcmil
Conductor - AL Str Size	1351.5 KCMIL - 1510 KCMIL
Conductor - AL Str Size Range	1351.5 KCMIL - 1510 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

Product Assets

Catalogs - BURNDY Master Catalog - Section I - Transmission
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_YNS-RT_LINEART_BW
Sales Drawings - SD058033-01
Specifications - YNS52RT

©2024 Hubbell Incorporated. All rights reserved