


**For Use in Raised Access or Wood Floors** Inches (mm)

AFB series boxes are available from our factory as pre-wired assemblies with CONNEXION modular plug-n-play system

**Style**



**Box Type**

<b>Round</b>	<b>RAFB4BASE</b>
<b>Min. Depth from Top of Floor Tile</b>	6.47" (164.3)
<b>Cu. In. (cm<sup>3</sup>) Capacity per Gang</b>	28.5 cu. in. (460 cm <sup>3</sup> )
<b>Dimensions - A</b>	6.41" (162.9)
<b>Dimensions - B</b>	7.33" (186.2)
<b>Dimensions - C</b>	8.05" (204.6)
<b>KO Trade Size: Sides</b>	(2) 1/2" (2) 3/4", 1 1/2" Concentric, (2) 1", 1 1/4" Concentric
<b>Bottom</b>	(1) 1 1/2", 2" (1) 3/4", 1" Concentric, (1) 3/4", 1", 1 1/4" Concentric
<b>Floor Thickness</b>	.71" (19.1) - 2.50" (63.5)
<b>Temporary Cover Included</b>	✓
<b>ADA</b>	Flange thickness is 8" thick and complies with ADA requirements

**RAFB4 Series Round Floor Box with Cover**

Includes RAFB4BASE and 8" cover.  
\*Covers are UL 514A listed; max. static load of 1,000lb with 2x safety factor



<b>Cover Finish</b>	<b>Catalog No.</b>
Brushed Aluminum	<b>RAFB4ALU</b>
Black Powder Coat	<b>RAFB4BLK</b>
Brass Plated	<b>RAFB4BRS</b>
Bronze Plated	<b>RAFB4BRZ</b>
Gray Powder Coat	<b>RAFB4GRY</b>
Satin Nickel Plated	<b>RAFB4NKL</b>

- Covers are of die cast aluminum construction
- UL514 Listed
- Max. static cover load of 1,000 lbs. w/2x safety factor\*

**8 Inch Round Covers**

Round covers are suitable for use with all floor types

<b>Finish</b>	<b>Catalog No.</b>
Brushed Aluminum	<b>CFBS1R8CVRALU</b>
Black Powder Coat	<b>CFBS1R8CVRBLK</b>
Brass Plated	<b>CFBS1R8CVRBRS</b>
Bronze Plated	<b>CFBS1R8CVRBRZ</b>
Gray Powder Coat	<b>CFBS1R8CVRGRY</b>
Satin Nickel Plated	<b>CFBS1R8CVRNKL</b>



\*Load applied through a 3" (76mm) mandrel in center of the cover.

**RAFB4 Series Plates**

Finish is Powder Coat White

<b>Plate Style</b>	(1) Decorator	(1) Duplex	(1) Simplex Opening 1.40 in. Diameter	(1) Twist-Lock® Opening 1.60 in. Diameter	Blank
<b>Cat. No.</b>	<b>RAFB4SPDECO</b>	<b>RAFB4SPDUPLEX</b>	<b>RAFB4SPTL14</b>	<b>RAFB4SPTL16</b>	<b>RAFB4SPBLANK</b>
<b>Plate Style</b>	(1) Hubbell iSTATION Opening for 3 Units	(3) Extron® MAAP Modules	(2) Extron® AAP Modules	Opening to Accept Bezels for Ortronics TracJack®	
<b>Cat. No.</b>	<b>RAFB4SP3UIS</b>	<b>RAFB4SP3MAAP</b>	<b>RAFB4SP2AAP</b>	<b>RAFB4SPORT</b>	

Note: Extron® is a registered trademark of Extron Electronics. Crestron® is a registered trademark of Crestron Electronics, Inc. TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.