YSR26FX4CFXLTCKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 2/0 Flex/AWG, Barrel B: 4 Flex/AWG

By Burndy
Catalog # YSR26FX4CFXLTCKITC

CU Splice Reducer, Barrel A 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, Barrel B 4 Flex G,H,I,K,M,DLO, 4 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Black/Gray Color Code, 13/8 Die Index.

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

General

Catalog Number	YSR26FX4CFXLTCKITC
Color Code	Black, Gray
Color Code - Side A	Black
Color Code - Side B	Gray
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	13/8
Die Index - Element A	13
Die Index - Element B	8
Die Index Run Side	13
Die Index Tap Side	8
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810429433
UPC 12 Digit	7818104294333

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.16 in
Dimension - L Length Overall mm	63 mm
Dimension - Length BB inch	0.74 in
Dimension - Length Overall inch	2.56 in
Dimension - Strip Length inch	1.10 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	2/0 AWG
Conductor - Copper Flex G Size A	2/0 AWG
Conductor - Copper Flex G Size B	4 AWG
Conductor - Copper Flex G Tap	4 AWG
Conductor - Copper Flex H Run	2/0 AWG
Conductor - Copper Flex H Size A	2/0 AWG
Conductor - Copper Flex H Size B	4 AWG
Conductor - Copper Flex H Tap	4 AWG
Conductor - Copper Flex I Run	2/0 AWG
Conductor - Copper Flex I Size A	2/0 AWG
Conductor - Copper Flex I Size B	4 AWG
Conductor - Copper Flex I Tap	4 AWG
Conductor - Copper Flex K Run	2/0 AWG

Conductor - Copper Flex K Size A	2/0 AWG
Conductor - Copper Flex K Size B	4 AWG
Conductor - Copper Flex K Tap	4 AWG
Conductor - Copper Flex M Run	2/0 AWG
Conductor - Copper Flex M Size A	2/0 AWG
Conductor - Copper Flex M Size B	4 AWG
Conductor - Copper Flex M Tap	4 AWG
Conductor - Copper Str Size	2/0 AWG-4 AWG
Conductor - Copper Str Size A	2/0 AWG
Conductor - Copper Str Size B	4 AWG
Conductor - Copper Str Size B Range	4 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG-4 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG-4 AWG

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	2880

Product Assets

3D Models - YSR26FX4CFXLTCKITC_MODEL-PDF
3D Models - YSR26FX4CFXLTCKITC_MODEL-STEP
3D Models - YSR26FX4CFXLTCKITC_MODEL-IGES
Catalogs - BURNDY Master Catalog - Section C - Compression Connections
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Installation Manuals - SPLICE KIT trilingual
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - 10021428
Specifications - YSR26FX4CFXLTCKITC

©2024 Hubbell Incorporated. All rights reserved