















PB2 BaseTrak® Inches (mm)

PB2 BaseTrak®	Description	Color	Length	Catalog No.	Description	Color	Length	Catalog No.	
	Base Two channel raceway. Available in 5ft (1.5m) and 10ft (3m) lengths. Assembled cover and base dimensions. W: 4.50" (114.30) H: 1.63" (41.40)	Office White	5ft 10ft	PB2B5 PB2B10	A: 1.42" (36.07) B: 4.50" (114.30)	Cover Cover allows access to multiple channels. Available in 5ft (1.5m) and 10ft (3m) lengths.	Office White	5ft 10ft	PB2C5 PB2C10
					Split Cover Cover allows separation of channels and access to a single channel. Available in 5ft (1.5m) and 10ft (3m) lengths. Two split covers are required for each raceway section.	Office White	5ft 10ft	PB2SPL5 PB2SPL10	B: 2.22" (56.39)
									

Device Boxes	Description	Color	Catalog No.
	2-Gang In-Line Box For switches, receptacles and communication devices. Provides flush look. See page U64 for recommended single gang KP plate options.	Office White	PB2IND2G
			

Fittings	Description	Color	Catalog No.	Description	Color	Catalog No.	
	Internal Elbow, Base and Cover Full capacity 1/4in bend radius internal elbow.	Office White	PB3IEBCA	A: 4.36" (110.74) B: 4.72" (119.89) C: 4.36" (110.74)	External Elbow, Base and Cover Full capacity 1/4in bend radius external elbow.	Office White	PB3EEBCA
							
Flat Elbow, Base and Cover Full capacity 1/4in bend radius flat elbow.	Office White	PB3FEBCA	A: 7.64" (194.66) B: 7.64" (194.66) C: 1.71" (43.43)	Tee, Base and Cover Full capacity 1/4in bend radius tee.	Office White	PB3TCBCA	A: 7.37" (187.20) B: 7.08" (179.83) C: 2.72" (69.09)
							
Splice Cover For covering potential openings where two lengths of raceway come together.	Office White	PB3SC	A: 1.56" (39.62) B: 4.74" (120.40) C: 1.69" (42.93)	Safety Strap For preventing potential tampering with PB2 BaseTrak cover. Can also be used as a splice cover.	Office White	PB3SS	A: 1.50" (38.10) B: 6.01" (152.65) C: 1.74" (44.20)
							
Conduit Adapter/Ceiling Fitting For connecting conduit to raceway. Also use for ceiling feeds. Has combination 1/2in, 3/4in, 1in, 1 1/4in and 1 1/2in trade size KOs.	Office White	PB2CACF	A: 4.72" (119.89) B: 5.22" (132.70) C: 6.30" (160.02)	Reducer Reduces from PB2 BaseTrak Raceway to PW2 WallTrak Raceway.	Office White	PB3REDA	A: 3.50" (88.90) B: 4.72" (119.89) C: 1.73" (43.94)
							
Transition Fitting Transitions horizontal PB2 BaseTrak to vertical PW2 WallTrak, PL1 LANTrak or PP1 PremiseTrak.	Office White	PB3TRBC	A: 3.22" (81.79) B: 7.28" (184.91) C: 2.42" (61.47)	Surface Panel Connector For connecting PB2 Raceway with surface type panel boxes.	Office White	PB3SPCA	A: 2.22" (56.39) B: 5.66" (143.76) C: 1.60" (40.64)
							
Wire Clip For holding conductors in place.	Office White	PB2WC	A: 1.29" (50.20) B: 1.00" (25.40)	End Cap For closing end of PB2 BaseTrak Raceway.	Office White	PB3ECA	A: 2.02" (51.31) B: 4.68" (118.97) C: 1.72" (43.69)
	