YTS48AT, ACSR - Full Tension Compression Splice

By Burndy
Catalog # YTS48AT

Al Full Tension Splice For Stranded Aluminum Transmission Line, 2000 kcmil, 345 kV, 735 Index, Extra High Voltage Applications.

General

Catalog Number	YTS48AT
Connector Type	Splice
Die Index	735
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810183106
UPC 12 Digit	7818101831066

Dimensions

Dimension - L Length Overall mm	585 mm
Dimension - Length Overall inch	23.02 in

Conductor Related

Conductor - AL Str Size	2000 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	240

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Catalogs - BURNDY Master Catalog - Section I - Transmission
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - SD061865-01
Specifications - YTS48AT

©2024 Hubbell Incorporated. All rights reserved