



①



②

Jack Panels, Unloaded

Includes cable management bar

Ports	Category	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Type	Catalog No.
24	-	1.72" (44)	19.00" (483)	1.24" (31)	Jack Panel	① NSPJ24
48	-	3.47" (88)	19.00" (483)	1.21" (31)	Jack Panel	② NSPJ48

Specifications

- cULus Listed
- Supports IEEE 802.3 10 Gigabit Ethernet applications
- Supports POE Applications
- Fast, reliable Cobra-Lock termination with no Punch Downs
- Compatible with our extensive line of work station plates & boxes, unloaded patch panels, & delivery systems products

netSELECT® Category 6A Jack with COBRA-LOCK Termination



Color	Single	24-Pack
Black	NSJU6ABK	NSJU6ABK24
Blue	NSJU6AB	NSJU6AB24
Gray	NSJU6AGY	NSJU6AGY24
Green	NSJU6AGN	NSJU6AGN24
Ivory	NSJU6AI	-
Light Almond	NSJU6ALA	-
Orange	NSJU6AOR	-
Red	NSJU6AR	-
White	NSJU6AW	NSJU6AW24
Yellow	NSJU6AY	-

netSELECT® Category 6, 5e and USOC Jacks

Specifications
TIA 568.2-D
Category
5e/6 Compliant
cULus Listed



Color	Modular Snap Fit Cat. 6 Single	Modular Snap Fit Cat. 6 24-Pack	Modular Snap Fit Cat. 5e Single	Modular Snap Fit Cat. 5e 24-Pack	Modular Snap Fit USOC
Black	NSJ6BK	NSJ6BK24	NSJ5EBK	NSJ5EBK24	NSJUBK
Blue	NSJ6B	NSJ6B24	NSJ5EB	NSJ5EB24	NSJUB
Gray	NSJ6GY	NSJ6GY24	NSJ5EGY	NSJ5EGY24	NSJUGY
Green	NSJ6GN	NSJ6GN24	NSJ5EGN	NSJ5EGN24	NSJUGN
Ivory	NSJ6I	NSJ6I24	NSJ5EI	NSJ5EI24	NSJUI
Light Almond	NSJ6LA	NSJ6LA24	NSJ5ELA	NSJ5ELA24	NSJULA
Orange	NSJ6OR	NSJ6OR24	NSJ5EOR	NSJ5EOR24	NSJUOR
Red	NSJ6R	NSJ6R24	NSJ5ER	NSJ5ER24	NSJUR
White	NSJ6W	NSJ6W24	NSJ5EW	NSJ5EW24	NSJUW
Yellow	NSJ6Y	NSJ6Y24	NSJ5EY	NSJ5EY24	NSJUY