PATRIOT® 15-Ton Latch Head Battery Actuated Crimper, Hydraulic Self-Contained, (2) 3.0Ah 18V Li-ion Batteries, 120V-AC Charger, Hard Case

By Burndy
Catalog # PAT46LWLI

PAT46 15T Latch Head Battery Crimper, 3Ah Li-ion, AC, Hard Case.

General

Application - For Use On	Copper, Aluminum, ACSR Terminals and Splices
Battery Type	3.0Ah 18V Li-Ion (Accepts 2.0Ah-6.0Ah Makita LI Batteries)
Catalog Number	PAT46LWLI
Container Type	Hard Case
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
EU RoHS Indicator	Under Review
Power Source	120V-AC Charger
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	
UPC	781810654675
UPC 12 Digit	7818106546755

Dimensions

Dimensions	18.59 in x 3.26 in x 13.93 in
Height	13.93 in
Jaw Width	2.00 in
Length	18.59 in
Weight	15.5 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC

Conductor Related

Crimping Ranges	Copper: #14 AWG Str. - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground Rod: 1/2"-1" diameter

Certifications And Compliance

Standards - RoHS Compliance Status	UI

Logistics

Package Contents	Crimper, (2) Batteries, Charger, Lanyard, Hard Case

Product Assets

Catalogs - Full Line BURNDY Catalog
Catalogs - Section N - Tooling
Customer Notices - Prop 65 Notice
Product Cross Section Image(s) - BUR_PAT46LW_LineArt
Sales Drawings - 50002858
SDS - Burndy BAT18VLI SDS Sheet (2022-02)

©2024 Hubbell Incorporated. All rights reserved.