BRYANT®

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 20A 480V AC, Watertight

By Bryant
Catalog # 320B7W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Flanged Inlet, 20A 480V AC, 2-Pole 3-Wire Grounding, Terminal Screw, Red, Watertight

Features

- Industrial Grade
- Male Flanged Inlet
- 20A 480V AC
- 2-Pole 3-Wire Grounding
- Terminal Screw

Application

High Ampacity Watertight Connections

General

Catalog Number	320B7W
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Inlet
UPC	781786250284

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	480 VAC
Voltage Rating Description	480V AC
Wattage	5540

Conductor Related

Number Of Wires	3-Wire

Product Assets

Specifications - 320B7W

©2024 Hubbell Incorporated. All rights reserved