BRYANT®

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 220-240V, Splash Proof

By Bryant
Catalog # 332R6S

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 220-240V, 2-Pole 3-Wire Grounding, Terminal Screw, Blue, Splash Proof

Features

- Industrial Grade
- Female Receptacle
- 32A 220-240V
- 2-Pole 3-Wire Grounding
- Terminal Screw

Application

High Ampacity Connections

General

Catalog Number	332R6S
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Splash Proof
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Splashproof - IP44
Type	Receptacle
UPC	781786252257

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Phase	Single Phase
Voltage Rating	380-415 V
Voltage Rating Description	380-415V
Wattage	8000

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA

Product Assets

Specifications - 332R6S

©2024 Hubbell Incorporated. All rights reserved