BRYANT®

# Locking Devices, Locking Devices, Industrial, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Black and White

By Bryant
Catalog # 4730

Locking Devices, Industrial, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Black and White

## Features

- Female Connector Body
- 15A 125V
- 2-Pole 3-Wire Grounding
- L5-15R
- Screw Terminal

## Application

Heavy Duty Industrial

## General

| | |
|---|---|
| Catalog Number | 4730 |
| Color | All Black |
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Insulation | Insulated Body |
| Item Type | 15A Regular Nylon Connector |
| Material | Composite |
| Material - Mounting Hardware | Cord Mounted |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Bryant |
| Style | Two-Piece Cord Clamp |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |
| Type | Connector Body |
| UPC | 781786656628 |

## Dimensions

| | |
|---|---|
| Dimensions | 1.53 in x 1.53 in x 2.78 in |
| Display Size | Standard Sized Product |
| Height | 2.78 in |
| Length | 1.53 in |
| Width | 1.53 in |

## Electrical Ratings

| | |
|---|---|
| Amperage Rating | 15 A |
| Connectivity | Screw Terminals |
| Current Rating | 15 A |
| Voltage Rating | 125 V |
| Voltage Rating Description | 125 V |

## Conductor Related

| | |
|---|---|
| Conductor Range | #14 AWG to #12 AWG |
| Number Of Wires | 3-Wire |
| Number of Conductors | 3-Wire Grounding |
| Wire Size | #14 AWG to #10 AWG |

## Certifications And Compliance

| | |
|---|---|
| Nema Rating | L5-15R |

## Logistics

| | |
|---|---|
| Carton Quantity | 10 |

## Product Assets

Catalog Page - BRY H-6 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - 4730



©2024 Hubbell Incorporated. All rights reserved