BRYANT®

Locking Devices, Industrial, Flanged Inlet, 30A 480V AC, 2-Pole 3-Wire Grounding, L8-30P, Screw Terminal, Black and White

By Bryant
Catalog # 70830MB

Locking Devices, Industrial, Flanged Inlet, 30A 480V AC, 2-Pole 3-Wire Grounding, L8-30P, Screw Terminal, Black and White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws
- Mounting screws included

Application

Heavy Duty Industrial

General

Catalog Number	70830MB
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Flanged Inlet
UPC	781786691162

Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Dielectric Strength	Withstands 3500V
Voltage Rating	480 VAC
Voltage Rating Description	480V AC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L8-30P

Logistics

Carton Quantity	10

Product Assets

Catalog Page - BRY Q-19 Catalog Page
Catalog Page - BRY H-11 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - 70830MB

©2024 Hubbell Incorporated. All rights reserved