BRYANT®

Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 4-Pole 4-Wire Non-Grounding, 60A 3-Phase 120/208V AC, 18-60R, Single Pack

By Bryant
Catalog # 8360FR

Straight Blade Devices, Receptacles, Flush Mount Single, Industrial Grade, 4-Pole 4-Wire Non-Grounding, 60A 3-Phase 120/208V AC,18-60R, Black, Single Pack

Features

- Flush Mount Single
- Industrial Grade
- 4-Pole 4-Wire Non-Grounding
- 60A 3-Phase 120/208V AC
- 18-60R

Application

Industrial Grade

General

Catalog Number	8360FR
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Bryant
Series	Heavy Duty
Style	Smooth Face
Type	Single Receptacle
UPC	781786673403

Dimensions

Dimensions	3.68 in x 2.25 in x 2.12 in
Display Size	Standard Sized Product
Height	2.12 in
Length	3.68 in
Weight	0.65 lb
Width	2.25 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Single Phase
Voltage Rating	Three Phase 120/208 VAC
Voltage Rating Description	3 Phase 120/208 VAC
Wattage	15000

Conductor Related

Number Of Wires	4-Wire
Wire Size	#6 AWG

Certifications And Compliance

Nema Rating	18-60R

Logistics

Carton Quantity	10

Product Assets

Catalog Page - BRY A-28 Catalog Page
Catalogs - Bryant Full Line Catalog
Literature - General Literature - Heavy Duty Straight Blade
Specifications - 8360FR

©2024 Hubbell Incorporated. All rights reserved