BRYANT®

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3- Wire Grounding, 5-20R

By Bryant
Catalog # BRY5369NC

Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3- Wire Grounding, 5-20R, Black, Single Pack

Features

- Heavy Duty
- Industrial/Commercial Grade
- Straight
- 20A 125V
- 2-Pole 3- Wire Grounding

Application

Extra Heavy Duty Industrial Grade

General

Catalog Number	BRY5369NC
Color	Black and White
Cord Range	0.300"-0.655"
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Industrial
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Plug
UPC	781786005952

Dimensions

Dimensions	2.95 in x 1.52 in x 1.38 in
Display Size	Standard Sized Product
Height	1.38 in
Length	2.95 in
Weight	0.15 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Nema Rating	5-20P

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

Catalog Page - BRY A-20 Catalog Page
Catalogs - Bryant Full Line Catalog
Literature - General Literature - Power Disruption Solutions
Literature - General Literature - TECH-SPEC® Plugs and Connectors
Literature - General Literature - BRYANT® Wiring Devices
Specifications - BRY5369NC

©2024 Hubbell Incorporated. All rights reserved