

Wisten

FINISH

- Brushed Nickel - 09
- Antique Bronze - 20

PAIR WITH

- Leap
- Chadwick
- Haven

ALSO IN

- Bath
- Close-to-Ceiling

WALL BRACKET

P2794-09 Brushed Nickel
4-1/2" W., 8-1/4" ht.,
Extends 6-1/4". H/CTR 4".
One medium base lamp, 100w max.

THREE-LIGHT FOYER

P3509-09 Brushed Nickel
12" dia., 25-7/8" ht.,
Overall ht. w/chain 101"; wire 15'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT

P3757-09 Brushed Nickel
18-1/4" dia., 25" ht.,
Overall ht. w/chain 100"; wire 15'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4434-09 Brushed Nickel
17" dia., 20-1/2" ht.,
Overall ht. w/chain 96"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER

P4435-09 Brushed Nickel
35" W., 12-1/2" D., 29" ht.,
Overall ht. w/stem 79"; wire 15'.
Four candelabra base lamps,
each 60w max

FIVE-LIGHT CHANDELIER

P4436-09 Brushed Nickel
22" dia., 26-3/8" ht.,
Overall ht. w/chain 101"; wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P4439-09 Brushed Nickel
27" dia., 33-3/8" ht.,
Overall ht. w/chain 156"; wire 15'.
Nine candelabra base lamps,
each 60w max.

MINI-PENDANT

P5108-09 Brushed Nickel
4" dia., 6-3/4" ht.,
Overall ht. w/stem 64"; wire 10'.
One medium base lamp, 100w max.

ONE-LIGHT PENDANT

P5112-09 Brushed Nickel
17" dia., 21-1/8" ht.,
Overall ht. w/chain 97"; wire 15'.
One medium base lamp, 100w max.

MINI-PENDANT

P5167-09 Brushed Nickel
3-3/4" dia., 9-3/4" ht. ,
Overall ht. w/stem 67"; wire 10'.
One medium base lamp, 100w max.



P3509-09



P4439-09



P4439-20



P3509-20



P3757-09



P5167-09



P4436-09



P4436-20



P5167-20



P3757-20



P5112-09



P5108-09



P4435-09



P4435-20



P5108-20



P5112-20



P4434-09



P2794-09

Wisten

WALL BRACKET

P2794-20 Antique Bronze
4-1/2" W., 8-1/4" ht.,
Extends 6-1/4". H/CTR 4".
One medium base lamp, 100w max.

THREE-LIGHT FOYER

P3509-20 Antique Bronze
12" dia., 25-7/8" ht.,
Overall ht. w/chain 101"; wire 15'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT PENDANT

P3757-20 Antique Bronze
18-1/4" dia., 25" ht.,
Overall ht. w/chain 100"; wire 15'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4434-20 Antique Bronze
17" dia., 20-1/2" ht.,
Overall ht. w/chain 96"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT LINEAR CHANDELIER

P4435-20 Antique Bronze
35" W., 12-1/2" D., 29" ht.,
Overall ht. w/stem 79"; wire 15'.
Four candelabra base lamps,
each 60w max

FIVE-LIGHT CHANDELIER

P4436-20 Antique Bronze
22" dia., 26-3/8" ht.,
Overall ht. w/chain 101"; wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P4439-20 Antique Bronze
27" dia., 33-3/8" ht.,
Overall ht. w/chain 156"; wire 15'.
Nine candelabra base lamps,
each 60w max.

MINI-PENDANT

P5108-20 Antique Bronze
4" dia., 6-3/4" ht.,
Overall ht. w/stem 64"; wire 10'.
One medium base lamp, 100w max.

ONE-LIGHT PENDANT

P5112-20 Antique Bronze
17" dia., 21-1/8" ht.,
Overall ht. w/chain 97"; wire 15'.
One medium base lamp, 100w max.

MINI-PENDANT

P5167-20 Antique Bronze
3-3/4" dia., 9-3/4" ht.,
Overall ht. w/stem 67"; wire 10'.
One medium base lamp, 100w max.



P2794-20



P4434-20

Wisten

Simple, modern and elegant, the Wisten family features a sculptured linear look. Etched glass for soft contemporary feel.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH

P2794-09 Brushed Nickel
P2794-20 Antique Bronze
4-1/2" W., 8-1/4" ht.
Extends 6-1/4". H/CTR 3-7/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P2795-09 Brushed Nickel
P2795-20 Antique Bronze
12-1/2" W., 8-1/4" ht.
Extends 6-1/4". H/CTR 5-1/2".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2796-09 Brushed Nickel
P2796-20 Antique Bronze
21" W., 8-1/4" ht.
Extends 6-1/4". H/CTR 5-1/2".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2797-09 Brushed Nickel
P2797-20 Antique Bronze
29-1/2" W., 8-1/4" ht.
Extends 6-1/4". H/CTR 6".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.



P2794-09



P2795-09



P2796-09



P2797-09



P2794-20



P2795-20



P2796-20



P2797-20

Wisten

Adds minimalist flair with metal clip detailing, clean etched glass and substantial decorative knob.

TWO-LIGHT FLUSH MOUNT

P3290-09 Brushed Nickel

P3290-20 Antique Bronze

14" dia., 7" ht.

Two medium base lamps,
each 100w max.



P3290-20



P3290-09