BRYANT®

Watertight Series, Locking Receptacle, 20A 3- Phase 250V AC, 3-Pole 4-Wire Grounding, NEMA L15-20R, Yellow

By Bryant
Catalog # BRY67W75

Watertight Series, Locking Receptacle, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, NEMA L15-20R, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

Performance

- Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes)
- UV resistance:All exposed materials are UV stabilized
- Flammability:UL94V0 (boxes, covers, and plates)

General

Catalog Number	BRY67W75
Color	Yellow
Item Type	20A Watertight Single Receptacle
Number Of Poles	3-Pole
Type	Receptacle
UPC	781786379275

Dimensions

Dimensions	4.56 in x 3.10 in x 3.45 in
Height	3.45 in
Length	4.56 in
Width	3.1 in

Electrical Ratings

Amperage Rating	20 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	• IP69K in use • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
Nema Rating	L15-20R

Logistics

Carton Quantity	10

Product Assets

Catalog Page - BRY I-6 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - BRY67W75

©2024 Hubbell Incorporated. All rights reserved