

# Emblem Round Recessed Trims LED

The Emblem Round LED recessed trim is ideal for use in both new construction as well as remodel/retrofit installations. Great for general ambient lighting applications. Offered in 4", 5" and 6" sizes and 4 finishes to match interior décor. The deep trim offers maximum glare control and the flat lens and bezel detail add a minimal and low profile look.

## TRIM FEATURES

- The trim is equipped with both Edison base adapter and quick link connector allowing easy installation in many standard medium based socket recessed housings and Progress LED recessed housings.
- A polycarbonate diffused lens reduces glare and pixilation from LEDs.
- Trim uses friction springs for easy installation into recessed housings.
- cCSAus Listed for Wet Locations, Energy Star.
- Flicker free dimming down to 10% with many Triac or ELV dimmers.
- Suitable for use in IC and Non IC applications.
- LEDs are 3000K, CRI 90+ and rated for 50,000 hours.

## 4" Round Trim

**P8080-09-30K** Brushed Nickel  
**P8080-20-30K** Antique Bronze  
**P8080-28-30K** White  
**P8080-31-30K** Black

Integrated LED, 630 lumens,  
66 lumens per watt, equivalent  
to 50W R20 incandescent lamp.



P8080-09-30K



P8080-20-30K



P8080-28-30K



P8080-31-30K

## COMPATIBLE RECESSED HOUSINGS

P830-LED  
P831-LED  
P832-LED  
P830-TG  
P831-AT  
P832-TG

## 5" Round Trim

**P8061-09-30K** Brushed Nickel  
**P8061-20-30K** Antique Bronze  
**P8061-28-30K** White  
**P8061-31-30K** Black

Integrated LED, 700 lumens,  
66 lumens per watt, equivalent  
to 65W BR30 incandescent lamp.



P8061-09-30K



P8061-20-30K



P8061-28-30K



P8061-31-30K

## COMPATIBLE RECESSED HOUSINGS

P84-LED  
P851-ICAT  
P1841-LED  
P1851-ICAT  
P1841-ICAT

## 6" Round Trim

**P8071-09-30K** Brushed Nickel  
**P8071-20-30K** Antique Bronze  
**P8071-28-30K** White  
**P8071-31-30K** Black

Integrated LED, 725 lumens,  
69 lumens per watt, equivalent  
to 65W BR30 incandescent lamp.



P8071-20-30K



P8071-28-30K



P8071-31-30K



P8071-09-30K

## COMPATIBLE RECESSED HOUSINGS

P87-AT  
P87-ATQC  
P87-LED  
P187-TG

All fixtures:

