BRYANT®

Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body, 6′ Cord

By Bryant
Catalog # BRY6MPS

Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body , 6′ Cord

Features

- 6) Receptacles
- Metallic Body
- 6′ Cord

Application

6 Outlet, Heavy Duty Devices

General

Catalog Number	BRY6MPS
Color	Office White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Plug Strips
Material	Steel
Material - Mounting Hardware	Portable
Number Of Outlets	6
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Series	Economy Power Strips (no SPD)
Type	Metallic
UPC	781786141599

Dimensions

Display Size	Standard

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cord Length	6 ft

Logistics

Carton Quantity	20

Product Assets

Catalog Page - BRY B-11 Catalog Page
Catalog Page - BRY D-5 Catalog Page
Catalogs - Bryant Full Line Catalog
Literature - General Literature - Surge Protection Devices
Specifications - BRY6MPS

©2024 Hubbell Incorporated. All rights reserved