

Edgelit Recessed LED

The LED edgelit recessed downlight combines a slim, low profile design with innovative technology, aesthetics, functionality and affordability. A separate recessed housing or junction box is not required for installation. The wet location listing allows for the product to be used in many applications, including showers. The low profile downlight is ideal for many residential, multi-family, commercial and hospitality applications. The detachable driver box can be removed from the fixture and mounted remotely when installing into shallow ceiling applications. The energy efficient design provides up to a 75% energy savings and up to 50,000 hours of LED life. The edgelit recessed luminaire can be dimmed down to 10%, flicker free, and is compatible with many forward phase (TRIAC) and electronic low voltage (ELV) dimmers.

TRIM FEATURES

- Features a detachable driver box, which can be mounted remotely for shallow ceiling installations.
- White polycarbonate lens controls direct glare from LEDs.
- No housing or J-box required for installation.
- Wet location listed.
- 120V input voltage.
- Dimmable to 10% with many Triac or ELV dimmers.
- IC rated and Air-Tight.
- Energy efficient design provides up to a 75% energy savings and up to 54,000 hours of LED life.
- Energy Star and Title 24 JA8-2016 listed.

5" LED EDGELIT

P800004-009-30 Brushed Nickel
P800004-020-30 Antique Bronze
P800004-028-30 White
P800004-031-30 Black
 5" W., 3" ht.
 9.5w integrated LED, 3000K, 90CRI, 550 lumens.



P800004-009-30



P800004-020-30



P800004-028-30



P800004-031-30

7" LED EDGELIT

P800005-009-30 Brushed Nickel
P800005-020-30 Antique Bronze
P800005-028-30 White
P800005-031-30 Black
 7" W., 3" ht.
 13w integrated LED, 3000K, 90CRI, 800 lumens.



P800005-009-30



P800005-020-30



P800005-028-30




P800005-031-30

All fixtures:



P800005-028-30
back view shown with
junction box attached



P800004-028-30
back view shown with
junction box attached

Edgelit Recessed Accessories


Progress lighting has released two new accessories for the Edgelit Recessed fixtures. P860040-028 - 18" extender cable allows for the junction box to be remote and mounted further away from the fixture. P860044 - rough in accessory allows for Edge Lit recessed fixtures to be used in new construction installations. This accessory ensures a mounting location after the dry wall is installed and can be used when building codes require that the luminaire is supported from the building structure

18" CABLE WITH TERMINALS

P860040-028 Satin White
 18" L., 1/2" dia.



P860040-028



EDGELIT RECESSED

ROUGH-IN ACCESSORY
P860044-001 Unfinished
 20" W., 9" ht.



P860044-001

