BRYANT®

Temporary Lighting Products, 45″ Fluorescent Light, 25W, 2125 Lumen Output, 25′ Cord

By Bryant
Catalog # BRYWL2525

Temporary Lighting Products, 45″ Fluorescent Light, 25W, 2125 Lumen Output, 25′ Cord

Features

- 25W
- 2125 Lumen Output
- 25′ Cord

General

Catalog Number	BRYWL2525
Light Output	2125 lm
Light Source	Fluorescent
Series	Portable work Light
Type	Fluorescent Worklight
UPC	781786379916

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Wattage	25 W

Conductor Related

Cord Length	25 ft

Product Assets

Literature - General Literature - Temporary Lighting Solutions Specifications - BRYWL2525

©2024 Hubbell Incorporated. All rights reserved