BRYANT®

Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 2 1/2"

By Bryant
Catalog # FC25090

Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 2 1/2"

Application

90 Degree Male

General

Catalog Number	FC25090
EU RoHS Indicator	No
Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	90 Degree With Male Fitting
UPC	781786241343

Dimensions

Conduit Trade Size	2 1/2 in

Electrical Ratings

Connectivity	Cap Nut

Certifications And Compliance

Nema Rating	Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Logistics

Carton Quantity	2

Product Assets

Catalog Page - BRY N-25 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - FC25090

©2024 Hubbell Incorporated. All rights reserved