BRYANT®

Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 3/4"

By Bryant
Catalog # FC75

Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 3/4"

Application

Straight Male

General

Catalog Number	FC75
EU RoHS Indicator	No
Material	Steel Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Between Enclosure and Conduit
OEM Brand Name	Hubbell Bryant
Series	Liquidtight Conduit
Style	For Metal & Non-Metallic PolyTuff I
Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
Type	Straight With Male Fitting
UPC	781786241046

Dimensions

Conduit Trade Size	3/4 in

Electrical Ratings

Connectivity	Cap Nut

Certifications And Compliance

Nema Rating	Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Logistics

Carton Quantity	10

Product Assets

Catalog Page - BRY N-25 Catalog Page
Catalogs - Bryant Full Line Catalog
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Literature - FOOD & BEVERAGE SOLUTIONS
Literature - FOOD & BEVERAGE SOLUTIONS
Literature - General Literature - BRYANT® Wiring Devices
Specifications - FC75

©2024 Hubbell Incorporated. All rights reserved