BRYANT®

Locking Devices, Industrial, Female Connector Body, 30A 28V DC, 2-Pole 3-Wire Grounding, FSL1R, Screw Terminal, Black and White

By Bryant
Catalog # FSL1NC

Locking Devices, Industrial, Female Connector Body, 30A 28V DC, 2-Pole 3-Wire Grounding, FSL1R, Screw Terminal, Black and White

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

General

Application	Heavy Duty Industrial
Catalog Number	FSL1NC
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Triple Gripper Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786638235

Dimensions

Dimensions	2.13 in x 2.13 in x 3.90 in
Display Size	Standard Sized Product
Height	3.9 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Voltage Rating	28 VDC
Voltage Rating Description	28 VDC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	FSL1-R

Logistics

Carton Quantity	10

Product Assets

Catalog Page - BRY H-14 Catalog Page
Catalogs - Bryant Full Line Catalog

A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved