BRYANT®

Locking Devices, Industrial, Male Plug, 30A 3- Phase Wye 120/208V AC 400Hz, 4-Pole 5-Wire Grounding, FSL4P, Screw Terminal, Black and White

By Bryant
Catalog # FSL4NP

Locking Devices, Industrial, Male Plug, 30A 3-Phase Wye 120/208V AC 400Hz, 4-Pole 5-Wire Grounding, NEMA FSL4, Screw Terminal, Black and White.

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention
- Designed, tested and approved for use on 400 Hz (400 cycles per second) circuits

Application

Extra Heavy Duty Industrial

General

Catalog Number	FSL4NP
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Triple Gripper Nylon Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Type	Plugs
UPC	781786638334

Dimensions

Dimensions	2.13 in x 2.13 in x 2.86 in
Display Size	Standard Sized
Height	2.86 in
Length	2.13 in
Width	2.13 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Phase	Three Phase
Voltage Rating	3 Phase Y 120/208 V
Voltage Rating Description	3 Phase Y 120/208 V

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	FSL4-P

Logistics

Carton Quantity	10
Pallet Quantity	2080

Product Assets

Catalog Page - BRY H-14 Catalog Page
Catalogs - Bryant Full Line Catalog
Specifications - FSL4NP

©2024 Hubbell Incorporated. All rights reserved