BRYANT®

Fiber Optic Panel Adapter, 6-Fiber, 3) LC Duplex, Phosphor Bronze Sleeves, Aqua

By Bryant
Catalog # FSPLCDM3AQ

Fiber Optic Panel Adapter, 6-Fiber, 3) LC Duplex, Phosphor Bronze Sleeves, Aqua

Features

- Premium Quality and High Performance Design

Application

Interconnect

General

Adapter Type	LC Duplex
Catalog Number	FSPLCDM3AQ
Color	Aqua
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	3) LC Duplex
Material	Phosphor Bronze
Material - Mounting Hardware	Snap-In
Number Of Ports	6
Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	MM
Temperature Rating	-40C to +85C
UPC	662620103051

Dimensions

Display Size	5.1″ X 1.1″

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

Certifications And Compliance

Industry Standard(s)
- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity	4

Product Assets

Specifications - FSPLCDM3AQ

©2024 Hubbell Incorporated. All rights reserved