BRYANT®

Fiber Optic Panel Adapter, 8 Fiber, 8) SC MTJR, Unloaded

By Bryant
Catalog # FSPSC8X

Fiber Optic Panel Adapter, 8 Fiber, 8) SC MTJR, Unloaded

Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

General

Adapter Type	SC Simplex/LC Duplex
Application	Interconnect
Catalog Number	FSPSC8X
Color	Black
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	SC Simplex/LC Duplex
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Number Of Ports	8
Performance	Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical) Environmental - Operating temperature - 0 ºC to +75 ºC
Repeatability	0.1 dB
Service Life	500 matings
Sub Brand	OptiChannel
Temperature Rating	-40C to +85C
UPC	662620218397

Dimensions

Display Size	5.1″ X 1.1″

Electrical Ratings

Connectivity	Receptacle
Insertion Loss	0.30 dB
Return Loss	26

Conductor Related

Fiber Size	125 Micron

Certifications And Compliance

Industry Standard(s)	TIA-568-C.3 TIA-604-FOCIS

Logistics

Carton Quantity	4

Product Assets

Catalog Page - PREM G11 CatalogPage
Catalogs - Premise Wiring Catalog
Literature - FIBERHUBB N-Series Fiber Panels

A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-FSPSC8X-SPEC-EN | REV 6/2024