BRYANT®

Power Protection Products, GFCI, Receptacle, Blank Face, 20A 125V, HP Rated, Ivory

By Bryant
Catalog # GFBFHP20I

Power Protection Products, GFCI,Receptacle, Blank Face, 20A 125V, HP Rated, Ivory

Features

- Blank face 1.5 horsepower motor control rated switch UL508 listed. Also listed to Underwriters Laboratories standard 943 for Class A GFCI
- If wired incorrectly there will be no power to the face or to downstream receptacles for added safety. (2) LED indicators provide immediate status of power, trip condition and ability to provide GFCI protection
- In addition to providing Class A GFCI protection, the HP series includes a 1.5 HP rating for motor control switching per UL508

General

Catalog Number	GFBFHP20I
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Style	Blank Face, 1.5HP
Type	Standard
UPC	883778450044

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Logistics

Carton Quantity	10

Product Assets

Catalog Page - WDK K-8 Catalog Page
Catalogs - WDK Catalog Full 2024
Specifications - GFBFHP20I

©2024 Hubbell Incorporated. All rights reserved