BRYANT®

Power Protection Devices, Self Test Faceless GFCI, 20A 125V, 2-Pole 3-Wire Grounding, Almond

By Bryant
Catalog # GFBFST20AL

Power Protection Devices, Self Test Faceless GFCI, 20A 125V, 2-Pole 3-Wire Grounding, Almond

Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Triple wipe construction

General

Catalog Number	GFBFST20AL
Color	Almond
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Blank Face
Type	Standard
UPC	883778122163

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements

Logistics

Carton Quantity	10

Product Assets

Literature - 2015 UL GFCI Requirements
Literature - CIRCUITPRO® Self Test GFCI
Sales Drawings - WDK_GFBFST20_DRAWING_PDF
Specifications - GFBFST20AL

©2024 Hubbell Incorporated. All rights reserved