BRYANT®

Replaced By GFRTR15LA - Heavy Duty Commercial Tamper-Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, Light Almond

By Bryant
Catalog # GFTRST15LA

Power Protection Devices, Receptacle, Self Test, GFCI, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Light Almond

General

Catalog Number	GFTRST15LA
Color	Light Almond
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Standard
Type	Tamper-Resistant
UPC	883778122293

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
Pallet Quantity	2240

Product Assets

Catalog Page - WDK Z-8 Catalog Page
Catalog Page - WDK K-4 Catalog Page
Catalogs - WDK Catalog Full 2024
Literature - 2015 UL GFCI Requirements
Literature - AUTOGUARD® Self Test Ground Fault Receptacles
Literature - CIRCUITPRO® Self Test GFCI
Sales Drawings - WDK_GFTRST15LA_DRAWINGS_PDF
Specifications - GFTRST15LA

©2024 Hubbell Incorporated. All rights reserved