BRYANT®

Power Protection Devices, Receptacle, Self Test, GFCI, IG, TRWR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown

By Bryant
Catalog # GFTWRST20IG

Power Protection Devices, Receptacle, Self Test, GFCI, IG, TRWR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown

General

Catalog Number	GFTWRST20IG
Color	Brown
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Isolated Ground
Type	Tamper-Resistant, Weather Resistant
UPC	883778122842

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
Pallet Quantity	2240

Product Assets

Catalog Page - WDK Z-8 Catalog Page
Catalog Page - WDK K-7 Catalog Page
Catalogs - WDK Catalog Full 2024
Literature - 2015 UL GFCI Requirements
Literature - CIRCUITPRO® Self Test GFCI
Sales Drawings - WDK_GFTWRST20IG_DRAWINGS_PDF
Specifications - GFTWRST20IG

©2024 Hubbell Incorporated. All rights reserved