

Blanco LED

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012

- Matte Black - 031
- Faux White Marble - 150

ALSO IN

Sconces

P300150-150-30


The Blanco Collection highlights classic forms with crisp, contemporary updates. Offered in a variety of metal finishes, each fixture features a thin, horizontal cylinder shade for a clean, linear design. Blanco LED is ideal for modern and transitional settings.



22" LINEAR LED BATH
P300150-150-30 Faux White Marble
 Installs horizontal or vertical.
 22-1/4" W., 4-3/4" ht.
 Extends 3-5/8". H/CTR 2-3/8".
 36w integrated LED, 3000K,
 90CRI, 1942 delivered lumens.

32" LINEAR LED BATH
P300151-150-30 Faux White Marble
 Installs horizontal or vertical.
 32-3/8" W., 4-3/4" ht.
 Extends 3-3/4". H/CTR 2-3/8".
 53w integrated LED, 3000K,
 90CRI, 2768 delivered lumens.

LED WALL BRACKET
P710047-150-30 Faux White Marble
 4-3/4" W., 11-3/4" ht.
 Extends 3-5/8". H/CTR 8-3/8".
 16w integrated LED, 3000K,
 90CRI, 823 delivered lumens.



All fixtures:



Blanco LED

22" LED LINEAR BATH
P300150-009-30 Brushed Nickel
P300150-012-30 Satin Brass
P300150-031-30 Matte Black
 Installs horizontal or vertical.
 22-1/4" W., 4-3/4" ht.
 Extends 3-5/8". H/CTR 2-3/8".
 36w integrated LED, 3000K,
 90CRI, 1942 delivered lumens.

32" LED LINEAR BATH
P300151-009-30 Brushed Nickel
P300151-012-30 Satin Brass
P300151-031-30 Matte Black
 Installs horizontal or vertical.
 32-3/8" W., 4-3/4" ht.
 Extends 3-5/8". H/CTR 2-3/8".
 53w integrated LED, 3000K,
 90CRI, 2768 delivered lumens.

LED WALL BRACKET
P710047-009-30 Brushed Nickel
P710047-012-30 Satin Brass
P710047-031-30 Matte Black
 4-3/4" W., 11-3/4" ht.
 Extends 3-5/8". H/CTR 8-3/8".
 16w integrated LED, 3000K,
 90CRI, 823 delivered lumens.

All fixtures:



Blanco LED

An elegantly modern effect is achieved with a design that minimizes all visible hardware.

P710047-009-30 Brushed Nickel
P710047-012-30 Satin Brass
P710047-031-30 Matte Black
P710047-150-30 Faux White Marble
4-3/4" W., 11-3/4" ht., wire 6".
Extends 3-5/8". H/CTR 8-3/8".
16w Integrated LED, 3000K,
90CRI, 823 delivered lumens.



P710047-009-30



P710047-012-30



P710047-031-30



P710047-150-30