BRYANT®

Heavy Duty Products, Single Pole Devices, Industrial Grade, Double Female, Coupler, 400A 600V AC/DC, Single Conductor, Pre-Wired, Orange

By Bryant
Catalog # HBLDFO

Heavy Duty Products, Single Pole Devices, Industrial Grade, Double Female, Coupler, 400A 600V AC/DC, Single Conductor, Pre-Wired, Orange

Features

- Industrial Grade
- Double Female
- Coupler

Application

High Ampacity

Performance

- Electrical - Amperage Rating - 400A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of the device

General

Catalog Number	HBLDFO
Color	Orange
EU RoHS Indicator	Contact Manufacturer
Insulation	Insulated Body
Item Type	Gender Reverser
Material	Brass and Elastomer
Number Of Pins	1) In, 1) Out
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Series 16
Specifications	• Accessory Item - Double Male Coupler • Body Material - Thermoplastic Elastomer • Contact Material - Brass • Product Type - Accessories
Style	Double Female
Type	Gender Reversing Devices
UPC	783585003382

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Current Rating	400 A
Voltage Rating Description	600V AC/DC
Wattage	360000

Certifications And Compliance

Industry Standard(s)	UL 498 And UL1691

Logistics

Carton Quantity	10

Product Assets

Catalog Page - WDK H-8 Catalog Page
Catalogs - WDK Catalog Full 2024
Catalogs - Bryant Full Line Catalog
Literature - Single Pole Devices
Specifications - HBLDFO

©2024 Hubbell Incorporated. All rights reserved