

# Wish LED

## FINISHES

- Antique Bronze - 20
- Black - 31

P6085-3130K9



*Craftsman  
Details*

*Black  
Finish*

*Etched White Linen Glass*

Wish maximizes aesthetics in outdoor areas for those who desire to preserve the exterior environment. Included dark sky shield provides full cut off illumination or remove for a traditional lighting effect. Antique Bronze finish has etched amber linen glass. Black finish has etched white linen glass.



P6084-3130K9



P6084-2030K9



P6085-3130K9



P6085-2030K9



P6424-3130K9\*



P6424-2030K9\*

### SMALL WALL LANTERN

**P6084-2030K9** Antique Bronze

**P6084-3130K9** Black

7" W., 10-3/8" ht.

Extends 8-5/8". H/CTR 3-1/8".

One 9w LED module, 3000K, 90CRI, 623 source lumens.

### MEDIUM WALL LANTERN

**P6085-2030K9** Antique Bronze

**P6085-3130K9** Black

9" W., 12-1/2" ht.

Extends 10-1/2". H/CTR 3-1/8".

One 17w LED module, 3000K, 90CRI, 1211 source lumens.

### POST LANTERN\*

**P6424-2030K9** Antique Bronze

**P6424-3130K9** Black

Dark Sky shield not included.

9" dia., 15-1/4" ht.

Fits 3" post (sold separately).

One 9w LED module, 3000K, 90CRI, 623 source lumens.



Dark sky cylinder included, except the post lantern.

All fixtures:



\*Post lantern is not Dark Sky Compliant.

# Wish

## FINISHES

- Antique Bronze - 20
- Black - 31

P6524-20



*Antique  
Bronze*

*Traditional  
Design*

*Etched Amber Linen Glass*



P6524-31



P6524-20



P6084-31



P6084-20



P6085-31



P6085-20



P6424-31\*



P6424-20\*

### SMALL WALL LANTERN

**P6084-20** Antique Bronze

**P6084-31** Black

7" W., 10-3/8" ht.

Extends 8-5/8". H/CTR 3-1/8".

One medium base lamp, 75w max.

### MEDIUM WALL LANTERN

**P6085-20** Antique Bronze

**P6085-31** Black

9" W., 12-1/2" ht.

Extends 10-1/2". H/CTR 3-1/8".

One medium base lamp, 100w max.

### POST LANTERN\*

**P6424-20** Antique Bronze

**P6424-31** Black

Dark Sky shield not included.

9" dia., 15-1/4" ht.

Fits 3" post (sold separately).

One medium base lamp, 100w max.

### HANGING LANTERN

**P6524-20** Antique Bronze

**P6524-31** Black

9" dia., 12-1/2" ht.

Overall ht. w/chain 87-1/2"; wire 15'.

One medium base lamp, 100w max.



Dark sky cylinder included, except the post lantern.

\*All fixtures except post lantern:

